

Toolless Shielded Cat6a Keystone Jack, PoE/PoE+ Compliant, Shuttered - Silver, TAA

MODEL NUMBER: N238-001-SH-TFA



Terminate your shielded Cat6a wall jack without using a punchdown tool. Ideal for wallplates, patch panels and surface-mount boxes.

Description

Strengthen your high-speed network with Tripp Lite's N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack. Terminate your Cat6a wall jack without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in wallplates, patch panels and surface-mount boxes. Power over Ethernet Plus (PoE+) compliant. RJ45 port is compatible with all Shielded Cat6a cables, and toolless punchdown connection is compatible with 22-24AWG Solid Wire cabling. The N238-001-SH-TFA's protective housing is fully shielded to reduce EMI/RFI interference that can damage or degrade data.

Features

Strengthens Your High-Speed Network Ideal for wallplates, patch panels and surface-mount boxes Lets you terminate your Cat6a wall jack without using a punchdown tool Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling RJ45 port compatible with all Shielded Cat6a cables Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
Superior Construction for Superior Performance Fully shielded housing cuts down on EMI/RFI interference that can damage or degrade data Features a shutter / dust cap that protects from dust and contaminants when not in use UL-listed Meets all EIA/TIA Cat6a requirements
TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing

Highlights

- Easy to terminate—no punchdown tool required
- Protective shielded housing reduces EMI/RFI interference
- Features a shutter / dust cap that protects from dust and contaminants when not in use
- Keystone design for use with wallplates, patch panels and surface mount boxes
- Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
- Meets all EIA/TIA Cat6a requirements

Package Includes

- N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack, PoE+ Compliant, Silver

Specifications

| OVERVIEW | |
|------------|----------------------|
| UPC Code | 037332189967 |
| Technology | Cat5/5e; Cat6; Cat6a |
| PHYSICAL | |
| Color | Silver |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------------------|
| Shipping Dimensions (hwd / cm) | 12.70 x 10.16 x 1.27 |
| Shipping Dimensions (hwd / in.) | 5.00 x 4.00 x 0.50 |
| Shipping Weight (kg) | 0.03 |
| Shipping Weight (lbs.) | 0.06 |
| CONNECTIONS | |
| Ports | 1 |
| Side A - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 1 | 110 IDC |
| PoE Type | Type 3 PoE++/UPoE (60W, IEEE 802.3bt) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N238-001-SH-TFA](#)