

Cat6a 10G Certified Pre-Terminated Copper Trunk Assembly (6x RJ45 F/F), Blue, 10 ft. (3.05 m)

MODEL NUMBER: **N261-010-6FF-BL**



Factory-terminated copper trunk assembly combines 6 certified Cat6a cables to save time, space and money. Ideal for data centers and other areas where quick installation and consistent network connection are important.

Description

The N261-010-6FF-BL Augmented Cat6/Cat6a Pre-Terminated Copper Trunk Bundle (F/F) makes installation a breeze and saves you time, space and money. All termination, bundling and testing is done at the factory, so almost anyone can do the installation in your data center in less time. Six certified and channel-tested Cat6a cables are bundled together, which cuts down on cable clutter in your cabinet. Both ends feature an unshielded female RJ45 keystone jack.

Designed for easy patching in switches and patch panels, this 10-ft. (3.05 m) assembly is constructed using 23 AWG solid conductor wire with a blue CMR-rated PVC jacket. Black mesh tubing keeps the cable neat and protects against fraying and damage. The 18-inch breakout legs are labeled on the ends for quick identification. System components meet or exceed ANSI/TIA-568-C.2 category requirements for performance. Backward compatible with Cat6 and Cat5e installations.

Features

Combines 6 Certified Cat6a Cables in One Bundle

- 100% terminated, bundled and tested at the factory
- Ideal for data centers and other areas where quick installation and consistent network connection are important
- Designed for easy connection in switches and patch panels
- Saves time, space and labor costs

Highlights

- 100% factory-terminated, -bundled and -tested
- 6 certified Cat6a cables per bundle
- Unshielded female RJ45 connectors on each end
- 23 AWG solid conductor wire with CMR-rated PVC jacket
- Meets or exceeds ANSI/TIA-568-C.2 standards

Package Includes

- N261-010-6FF-BL Augmented Cat6/Cat6a Pre-Terminated Copper Trunk Bundle (F/F), 10-ft. (3.05 m)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Top-of-the-Line Construction

- Unshielded female RJ45 connectors on each end
- 23 AWG solid conductor wire
- Blue CMR-rated PVC jacket
- Black mesh tubing keeps cables neat and protects against fraying and damage
- 18 in. breakout legs labeled on ends for quick ID

Fully Compliant and Compatible

- Meets or exceeds ANSI/TIA-568-C.2 category requirements for performance
- Backward compatible with Cat6 and Cat5e installations

Specifications

OVERVIEW	
UPC Code	037332196484
Technology	Cat6a
PHYSICAL	
Color	Blue
Cable Shielding	UTP
Cable Jacket Rating	CMR
Conductor Material	Solid Copper
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Cable Length (cm)	304.8
Shipping Dimensions (hwd / cm)	1.27 x 30.73 x 38.10
Shipping Dimensions (hwd / in.)	0.50 x 12.10 x 15.00
Shipping Weight (kg)	1.45
Shipping Weight (lbs.)	3.20
COMMUNICATIONS	
Network Speed	10Gbps
CONNECTIONS	
Side A - Connector 1	(6) RJ45 (FEMALE)
Side B - Connector 1	(6) RJ45 (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
Snagless Connector	No
STANDARDS & COMPLIANCE	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N261-010-6FF-BL](#)