

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 123M (405 ft.)

MODEL NUMBER: N320-405



### Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber
- Insertion loss testing performed on every connector (0.2dB typical)

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

### Package Includes

- 405-ft. (123.44 m) LC/LC Duplex MMF 62.5/125 Fiber Patch Cable

### Description

Tripp Lite's 405-ft. (123.44 m) multimode duplex micron fiber optic LC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC connectors on each end, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 405-ft. (123.44 m)
- Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

OVERVIEW	
UPC Code	037332140463
Technology	Multimode
Optical Mode	OM1



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Cable Jacket Color	Orange
Cable Jacket Rating	LSZH
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Cable Length (ft.)	405
Cable Length (m)	123.4
Cable Length (in.)	4860
Shipping Dimensions (hwd / cm)	25.65 x 11.94 x 26.16
Shipping Dimensions (hwd / in.)	10.10 x 4.70 x 10.30
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N320-405](#)