

Guaranteed compatibility when used with recommended Tripp Lite cabling. Designed specifically for use with Tripp Lite cables, such as the N846-Series cables.

100Gb/120Gb Pass-Through Cassette - (x12) 24-Fiber MTP/MPO (Female)

MODEL NUMBER: **N484-12M24**



Description

Tripp Lite's N484-12M24 is a High Density 100/120Gb Pass-through Cassette, with (x12) 24-Fiber MTP/MPO connections. Designed specifically for use with Tripp Lite's N484-00U and N484-01U chassis; up to 4 cassettes per N484-01U, or 1 per N484-00U. Guaranteed compatibility when used with recommended Tripp Lite cabling. Designed specifically for use with Tripp Lite cables, such as the N846-Series cables. Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory terminated connectors that reduce the time and labor required of field connector terminations. Cassette housing made with heavy duty, 1.0mm Cold Rolled Steel.

Features

- High Density Fiber Cassette for use with Tripp Lite's N484-00U and N484-01U chassis'
- 100/120Gb Pass-through Cassette, with (x12) 24-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N846-Series cables
- Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required
- Factory terminated connectors reduce the time and labor required of field connector terminations
- Housing made of heavy duty, 1.0mm Cold Rolled Steel
- Includes dust caps for unused ports

Specifications

Highlights

- High Density Fiber Cassette for use with Tripp Lite's N484-00U and N484-01U chassis'
- 100/120Gb Pass-through Cassette, with (x12) 24-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N846-Series cables
- Factory terminated connectors reduce the time and labor required of field connector terminations

System Requirements

- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N846-Series cables

Package Includes

- N484-12M24 100/120GbE Pass-Through Cassette - (x12) 24-Fiber MTP/MPO (Female)
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|-------------------------------------|---------------------------|
| UPC Code | 037332187208 |
| Technology | MTP/MPO |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / cm) | 5.99 x 13.00 x 3.71 |
| Shipping Dimensions (hwd / in.) | 2.36 x 5.12 x 1.46 |
| Shipping Weight (kg) | 0.22 |
| Shipping Weight (lbs.) | 0.49 |
| Unit Dimensions (hwd / in.) | 1.4 x 4.4 x 0.8 |
| Unit Weight (kg) | 0.14 |
| Unit Weight (lbs.) | 0.3 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 122 F (-20 to 50 C) |
| CONNECTIONS | |
| Ports | 12 |
| Side A - Connector 1 | 24-STRAND MTP (FEMALE) |
| Side B - Connector 1 | 24-STRAND MTP (FEMALE) |
| STANDARDS & COMPLIANCE | |
| Approvals | RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N484-12M24](#)