

Computer Power Cord, NEMA 5-15P to C13 - Heavy-Duty, 15A, 125V, 14 AWG, 12 ft. (3.66 m), Black

MODEL NUMBER: **P007-012**



Computer power cord connects a server, computer, monitor, printer or other device with a C14 inlet to an AC outlet on a PDU.

Features

5-15P to C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection This computer power supply cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. You can use it to connect a computer, server, monitor, laser printer or drive to a PDU, UPS, surge protector or AC wall outlet. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The 12-ft. (3.66 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering larger servers, laser printers and other network devices
- 12-ft. (3.66 m) length allows great flexibility in placing devices in relationship to AC outlet
- Computer power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, large servers and laser printers to a PDU up to 12 ft. away in your data center
- Extend an existing power connection up to 12-ft. (3.66 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P007-012 Desktop Computer Power Cord, 5-15P to C13, 12-ft. (3.66 m), Black

Specifications

OVERVIEW	
UPC Code	037332182548
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	12
Cable Length (m)	3.7
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Weight (kg)	0.54
Shipping Weight (lbs.)	1.19
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P007-012](#)