

## Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.91 m), Orange

MODEL NUMBER: **P018-003-AOR**



Connects a PDU or UPS system with a C14 input port to network hardware, such as computers, servers and storage drives, with C15 power connectors.

### Features

#### Safe, Reliable Power Solution

- Connects PDU or UPS system with C14 input to network hardware with C15 power connectors
- Ideal for replacing an old or lost cord
- Recommended for Cisco, HP and other C15-compatible hardware

#### Color-Coded Cable and Connectors

- Colored orange for easy identification in crowded rack or workstation

#### Optimum Construction

- 14 AWG wire
- Flexible SJT jacket
- 250V/15A rating
- UL-listed

## Specifications

OVERVIEW	
UPC Code	037332199126
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America

### Highlights

- Easy-to-identify orange SJT jacket and fully molded orange ends
- Flexible 14 AWG wire for easy routing
- 250V/15A rating
- UL-listed
- Recommended for Cisco®, HP and other C15-compatible hardware

### Package Includes

- P018-003-AOR Heavy-Duty Computer Power Cord, Orange, 3 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Orange
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Cable Length (cm)	91.44
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.44
ENVIRONMENTAL	
Operating Temperature Range	-4 F to 221 F (-20 TO 105 C)
Storage Temperature Range	-4 F to 221 F (-20 TO 105 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P018-003-AOR](#)