

Power Cord, C19 to NEMA L6-20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P040-006



Heavy-duty power cord supplies power to network devices that require a heavy-gauge connection, such as larger servers and switches.

Features

C19 to L6-20P Power Cable for Network Devices That Require a Heavy-Gauge Connection This 12 AWG power cable is designed for servers, routers, network switches, blade server enclosures and other devices that require a heavy-gauge connection capable of managing high power levels. The fully molded C19 end connects to your device's C20 inlet, and the fully molded NEMA L6-20P plug connects to an AC power source up to 6-ft. (1.83 m) away. The 6-ft. (1.83 m) length allows you some flexibility in placing equipment with respect to the power outlet.

Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L6-20P connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking connector is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the heavy-duty power cable always stays connected.

Highlights

- Recommended for powering servers, switches and other essential network devices
- Locking connector maintains secure link to avoid loss of power and costly downtime
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- C19 to L6-20P power cord is ideal replacement for worn-out or missing cable
- Long 6-ft. (1.83 m) cord provides flexibility in placing connected device away from outlet

Applications

- Connect network devices like servers, switches and blade server enclosures to a PDU up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Replace a worn-out or missing heavy-gauge power cord

Package Includes

- P040-006 C19 to L6-20P Power Cord, 6-ft. (1.83 m), Black

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332164902
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Cable Length (ft.)	6
Cable Length (m)	1.8
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 19.81
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 7.80
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
CONNECTIONS	
Side A - Connector 1	NEMA L6-20P
Side B - Connector 1	IEC-320-C19
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P040-006](#)