

Power Extension Cord/Splitter, NEMA L6-30P to 2x NEMA L6-30R Y Splitter, Heavy-Duty - 30A, 250V, 10 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: **P041-001-2**



L6-30P to L6-30R splitter allows two devices with NEMA L6-30P plugs to share one AC power input cord and one NEMA L6-30R outlet.

Features

Heavy-Duty Y-Style Splitter Cable Connects 2 Devices with L6-30P Plugs to One AC Outlet This Y splitter cable features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. With this extension cord splitter, a single NEMA L6-30R outlet can power two devices, such as PDUs, UPS systems, instrument amplifiers and other equipment compatible with a NEMA L6-30P plug. Ideal for areas where AC outlets are limited, such as rack cabinets or small network closets, this L6-30P to L6-30R Y splitter is compatible with Tripp Lite power and extension cords. The 1-ft. (0.31 m) length helps reduce cable clutter.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual PDUs, UPS systems or other heavy-duty devices
- Adds 1-ft. (0.31 m) to your existing power connection to provide flexibility in placing devices
- Locking connectors maintain secure link to avoid loss of power and costly downtime
- Thick 10 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect 2 devices like PDUs and UPS systems to one power outlet up to 1-ft. (0.31 m) away in your office or work space
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P041-001-2 L6-30P to 2x L6-30R Y Splitter, 1-ft. (0.31 m), Black

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332141484
Device Compatibility	PDU; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	30
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Cable Length (ft.)	1
Cable Length (m)	0.3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	40.13 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	15.80 x 11.80 x 0.50
Shipping Weight (kg)	1.09
Shipping Weight (lbs.)	2.40
CONNECTIONS	
Side A - Connector 1	NEMA L6-30P
Side B - Connector 1	(2) NEMA L6-30R
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P041-001-2](#)