

DisplayPort to VGA/HDMI All-in-One Converter Adapter, DP ver 1.2, 4K 30 Hz HDMI

MODEL NUMBER: **P136-06N-HV-V2**



All-in-one converter/adapter connects your DisplayPort-enabled laptop or tablet to a VGA or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

Description

No more carrying around separate adapters for various monitors, projectors and televisions. The P136-06N-HV-V2 DisplayPort 1.2 to VGA/HDMI All-in-One Converter Adapter connects your laptop or tablet's DisplayPort to a VGA or HDMI display. The simple all-in-one solution for displaying content on a larger screen, the P136-06N-HV-V2 is ideal for trade shows, classrooms, lecture halls and other presentations.

The all-in-one unit contains separate female HD15 and HDMI ports. It supports video resolutions up to 1920 x 1200, including 1080p @ 60 Hz (HD15), and 4K x 2K Ultra High Definition (UHD) up to 3840 x 2160 @ 24/30 Hz (HDMI). It also supports 36-bit Deep Color (12 bits per channel).

The P136-06N-HV-V2 is compatible with laptops, tablets and other devices equipped with a female DisplayPort. It's completely plug-and-play with no software or drivers to install or external power supply needed. With its small size and built-in cable, the P136-06N-HV-V2 is perfect for stowing in your laptop bag and carrying to school, the office or the latest trade show.

Features

Connects Your DisplayPort Laptop or Tablet to a VGA or HDMI Display

- Ideal for trade shows, classrooms, lecture halls and other presentations
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p @ 60 Hz
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)

Plug-and-Play Convenience

- No software or drivers to install

Highlights

- Separate HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K video resolutions @ 24/30 Hz
- The P136-06N-HV is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- The P136-06N-HV is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Package Includes

- P136-06N-HV-V2 DisplayPort 1.2 to VGA/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- No external power supply required
- Small enough to stow in laptop bag or briefcase
- The P136-06N-HV is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Specifications

OVERVIEW	
UPC Code	037332193216
Technology	HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	1.27 x 9.91 x 12.19
Shipping Dimensions (hwd / in.)	0.50 x 3.90 x 4.80
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P136-06N-HV-V2](#)