

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter (M/F), White, 6-in. (15.24 cm)

MODEL NUMBER: **P137-06N-VGA**



Connect a VGA monitor to a Mac or PC with a Mini Displayport output

Features

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Highlights

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

System Requirements

- Mac or PC with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Monitor with a VGA port
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-VGA-V2

Package Includes

- Mini-DisplayPort to Active VGA Adapter

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332158901
Technology	VGA/SVGA; DisplayPort
PHYSICAL	
Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 0.03
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.01
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.05
ENVIRONMENTAL	
Operating Temperature Range	0 C ~ 70 C
Storage Temperature Range	10 C ~ 80 C
Operating Humidity Range	10% ~ 85% RH
Storage Humidity Range	5% ~ 90% RH
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
STANDARDS & COMPLIANCE	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P137-06N-VGA](#)