

Mini DVI to VGA Cable Adapter, Video Converter for Macbooks and iMacs (M/F)

MODEL NUMBER: P138-000-VGA



Highlights

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length

System Requirements

- Apple Intel iMac, MacBook, or 12-inch PowerBook G4

Package Includes

8-inch mini-DVI to VGA Adapter

Description

Tripp Lites mini-DVI to VGA Female Video Adapter Cable allows you to connect a VGA Display to the mini-DVI port found on some Apple computer models. Supports resolutions up to 1920 x 1080 (1080i).

Features

- Connect a VGA Monitor to an Apple Intel iMac, MacBook, or 12-inch PowerBook G4 mini-DVI Port
- 8-inch overall length
- Supports video resolutions up to 1920 x 1080 (1080i)

Specifications

OVERVIEW	
UPC Code	037332176752
Technology	DVI; VGA/SVGA
PHYSICAL	
Color	White
Cable Length (ft.)	0.7
Cable Length (m)	0.2
Cable Length (in.)	8
Cable Length (cm)	20.32
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.13
CONNECTIONS	
Side A - Connector 1	MINI-DVI (MALE)
Side B - Connector 1	HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P138-000-VGA](#)