



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

In most applications where the HDMI cable exceeds 16 ft., a signal booster (B122-000-60) must be used with this cable to ensure a signal strong enough for your display.

HDMI Easy Pull Cable, Digital Video with Audio (M/M), 25 ft.

MODEL NUMBER: **P568-025-EZ**



Description

Tripp Lite's 25-foot (7.6-meter) HDMI Easy Pull Monitor Cable w/ Connectors makes running long video cables a snap. The pull-apart design allows the cable to run through conduit or other tight areas that a HDMI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8 inch. Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both HDMI male ends are molded and have integral strain relief to provide long life. UL20276 Digital Video Cable supports 1080p. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- 2-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- High quality quad-shielded cable with gold connectors and pins
- Bandwidth up to 10.2 Gbps - Full 1080p resolution as specified by HDMI 1.2
- In most applications where the HDMI cable exceeds 16 ft., a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- HDMI male to male molded connectors
- UL20276 Digital Video Cable
- Supports High Definition (HD) video resolutions up to 1080p

Specifications

Highlights

- 2-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- Bandwidth up to 10.2 Gbps - Full 1080p resolution
- Supports High Definition (HD) video resolutions up to 1080p

Package Includes

HDMI Easy Pull Cable, HD 1080p, Digital Video with Audio (M/M), 25 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332175564
Product Type	Passive
Technology	HDMI
VIDEO	
Max Supported Video Resolution	1920 x 1080 @60Hz
PHYSICAL	
Color	Black
Wire Gauge (AWG)	28
Cable Length (ft.)	25
Cable Length (m)	7.6
Shipping Dimensions (hwd / cm)	2.54 x 17.53 x 22.35
Shipping Dimensions (hwd / in.)	1.00 x 6.90 x 8.80
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P568-025-EZ](#)