

High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 1 ft. (0.31 m)

MODEL NUMBER: **P569-001**



Transmits digital audio/video and Ethernet signals from an HDMI source to a 4K-enabled television, projector or monitor. Ideal for home theater systems, digital signage and other applications that display UHD video.

Features

Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for home theater systems, digital signage and other applications that display UHD video and multi-channel audio

High Performance and Wide Compatibility

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K), including 1080p, and 3D
- Supports data transfer speeds up to 18 Gbps
- Audio return channel simplifies setup between display and receiver
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations
- Works in all HDMI cabling scenarios

Superior Construction Ensures a Flawless Signal

- Fully molded 30 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Corrosion-resistant gold-plated connectors and contacts for optimal signal transfer
- Flexible PVC jacket easy to install in tight spaces

Specifications

Highlights

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K)
- Supports data transfer speeds up to 18 Gbps
- Backward compatible with previous HDMI generations
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated connectors and contacts for optimal signal transfer

Package Includes

- P569-001 High-Speed HDMI Cable with Ethernet and Digital Video with Audio (M/M), 1 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332198280
Product Type	Passive
Technology	HDMI
PHYSICAL	
Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.3
Cable Length (in.)	12
Cable Length (cm)	30.48
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.76
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.75
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.08
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 °F (-10 to 50 °C)
Storage Temperature Range	5 to 140 °F (-15 to 60 °C)
Operating Humidity Range	0 to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P569-001](#)