

Standard Speed HDMI Cable with Ethernet, Digital Video with Audio (M/M), 50 ft. (15.24 m)

MODEL NUMBER: **P569-050**



Highlights

- 50-ft. (15.24 m) Standard Speed with Ethernet HDMI cable
- Supports transmission speeds up to 10.2Gbps
- Backward compatible to previous HDMI generations
- Video mirroring with iPad2

System Requirements

- HDMI video source and HDMI enabled TV / Monitor

Package Includes

50-ft. (15.24 m) Standard Speed with Ethernet HDMI Cable

Features

- 50-ft. (15.24 m) Standard Speed with Ethernet HDMI cable
- Supports transmission speeds up to 10.2Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

Specifications

OVERVIEW	
UPC Code	037332186041
Product Type	Passive
Technology	HDMI
PHYSICAL	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15.2
Shipping Dimensions (hwd / cm)	5.59 x 17.27 x 20.32
Shipping Dimensions (hwd / in.)	2.20 x 6.80 x 8.00



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.95
Shipping Weight (lbs.)	2.10
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P569-050](#)