

DisplayPort Cable with Latches, 4K @ 60 Hz, (M/M) 15 ft. (4.57 m)

MODEL NUMBER: **P580-015**



Highlights

- Digital Video and Audio in one cable
- Small footprint compared to VGA or DVI
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p

Package Includes

DisplayPort Monitor Cable - 15-ft. (4.57 m)

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p
- Supports High Definition Content Protection (HDCP)

Specifications

OVERVIEW	
UPC Code	037332145949
Product Type	Passive
Technology	DisplayPort
PHYSICAL	
Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.6
Shipping Dimensions (hwd / cm)	23.11 x 18.29 x 0.25
Shipping Dimensions (hwd / in.)	9.10 x 7.20 x 0.10
Shipping Weight (kg)	0.29



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	0.65
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
SPECIAL FEATURES	
Latching Connector	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P580-015](#)