



Requires Tripp Lite 3-phase auto-transfer switch (ATS) PDU (sold separately).

PDU330AT6L15PDU330AT6L1530PDU330AT6L2130PDU330AT6H50

8.6/12.6kW 3-Phase Vertical PDU Strip, 208V Outlets (42 C13 & 12 C19), 0U Rack-Mount, Accessory for Select ATS PDUs

MODEL NUMBER: PDU3V20D354A

Required rack-mounted vertical outlet strip accessory for select Tripp Lite 3-phase auto-transfer switch (ATS) PDUs. Distributes AC power to high-density equipment racks in data centers and server rooms.

Description

The PDU3V20D354A 8.6/12.6kW 3-Phase Vertical Power Distribution Unit (PDU) Outlet Strip is a required accessory option for Tripp Lite's PDU330AT6L15, PDU330AT6L2130, PDU330AT6L1530, PDU350AT6H50 and other 3-phase auto-transfer switch (ATS) PDUs that specify compatibility with this model. It's ideal for high-density equipment racks in data centers and server rooms.

When used with 208V ATS models with a 35A input rating (such as PDU350AT6H50), the PDU3V20D354A supports up to 12.6kW total output with 20A maximum full balanced load per phase combination output bank (L1-L2, L2-L3, L3-L1). When used with 208V ATS models with a 24A input rating (such as PDU330AT6L2130, PDU330AT6L1530 or PDU330AT6L15), it supports up to 8.6kW total output with 13.9A maximum balanced load per phase combination output bank.

The 42 C13 and 12 C19 single-phase outlets receive power from the connected ATS PDU. The outlets are interlaced to help you balance loads by spreading connections across the phase combinations (L1-L2, L2-L3, L3-L1) throughout the rack. Each outlet is numbered and color-coded to help you keep track of connected devices and which phase combination powers each. The 2.5-ft. (0.76 m) power cord with 8-position plug connects directly to the PDU's rear receptacle.

The PDU3V20D354A's rugged all-metal housing mounts in compatible racks in seconds with no tools needed. Vertical 0U installation reduces cord clutter and improves airflow through the rack.

Features

Required Accessory for Select Tripp Lite ATS PDUs

- Compatible with PDU330AT6L15, PDU330AT6L2130, PDU330AT6L1530, PDU350AT6H50 and other select Tripp Lite 3-phase ATS PDUs
- Ideal for high-density equipment racks in data centers and server rooms
- Supports up to 12.6kW total output with 20A maximum per output bank when connected to 208V ATS models with a 35A input rating (such as PDU350AT6H50)
- Supports up to 8.6kW total output with 13.9A maximum per output bank when connected to 208V ATS models with a 24A input rating (such as PDU330AT6L2130, PDU330AT6L1530 or PDU330AT6L15)
- Heavy-duty 2.5-ft. (0.76 m) power cord plugs directly into the ATS PDU with a Unique 8-position plug

Features 42 C13 and 12 C19 Interlaced C13 Outlets

- Single-phase outlets are interlaced to help you balance loads by spreading connections across the

Highlights

- Required for select Tripp Lite 3-phase ATS PDUs
- Offers 42 C13 and 12 C19 single-phase outlets
- Supports up to 8.6 or 12.6kW total output (depends on ATS PDU)
- Simplifies load balancing with interlaced, color-coded outlets
- Supports 0U toolless vertical rack mounting

Package Includes

- PDU3V20D354A 8.6/12.6kW 3-Phase Vertical PDU Outlet Strip



phase combinations (L1-L2, L2-L3, L3-L1) throughout the rack

- Numbered and color-coded for easy identification of connected devices and which phase combination output bank powers them

Installs Easily in 0U of Rack Space

- Preinstalled mounting buttons for toolless vertical rack-mounting in compatible racks
- Saves rack space, improves airflow and reduces cord clutter by locating outlets closer to connected devices
- Preinstalled ground screw for connecting devices that require chassis ground
- Heavy-duty all-metal housing provides durability and reliability in demanding high-density rack environments

Specifications

OVERVIEW	
UPC Code	037332190444
Product Type	0U Strip for 3-Phase ATS PDU
Accessories Type	0U Strip for 3-Phase ATS PDU
INPUT	
Maximum Input Amps	35
Input Phase	3-Phase
Input Cord Details	Includes 7 conductor input plug for use with compatible Tripp Lite ATS PDU products only
Input Cord Length (ft.)	2.5
Input Cord Length (m)	0.76
OUTPUT	
Output Capacity Details	Supports up to 12.6kW total output; 20A max per output phase (L1-L2, L2-L3, L3-L1) when used with 35A max 208V input ATS models (such as PDU350AT6H50); Supports up to 8.6kW total output; 13.9A max per output phase (L1-L2, L2-L3, L3-L1) when used with 24A max 208V input ATS models (such as PDU330AT6L2130, PDU330AT6L1530 and PDU330AT6L15); All configurations: 16A max per C19 outlet, 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(42) C13; (12) C19
Output Nominal Voltage	200; 208; 220; 230; 240
Overload Protection	n/a
PHYSICAL	
Form Factors Supported	Vertical rackmount installation supported with toolless mounting in button-mount compatible racks
Material of Construction	Metal



PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	12.95 x 16.51 x 194.06
Shipping Dimensions (hwd / in.)	5.10 x 6.50 x 76.40
Shipping Weight (kg)	6.56
Shipping Weight (lbs.)	14.46
Unit Dimensions (hwd / cm)	177.8 x 5.59 x 5.64
Unit Dimensions (hwd / in.)	70 x 2.2 x 2.22
Unit Weight (kg)	4.20
Unit Weight (lbs.)	9.26
ENVIRONMENTAL	
Operating Temperature Range	0 to 50C (32 to 122F)
Storage Temperature Range	-15C to 60C (5 to 140F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA), CSA (Canada), NOM (Mexico), FCC Class A (Emissions), ROHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDU3V20D354A](#)