



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

2.4kW Single-Phase Metered PDU, 120V (12 5-15/20R), L5-20P / 5-20P, 120V Input, 15 ft. (4.57 m) Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH20



Highlights

- Metered single phase 20A 120V PDU
- 1U horizontal rackmount; digital current meter
- NEMA 5-20P / L5-20P input; 15-ft. (4.57 m) line cord
- 12 NEMA 5-15/20R outlets
- Reversible housing; 4.5 in. / 11.4cm depth

Package Includes

- PDUMH20 Metered rackmount PDU
- L5-20R to 5-20P plug adapter
- Owner's manual with warranty information

Features

- 20A single phase 120V Metered Power Distribution Unit / PDU
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA L5-20P 20A 120V input plug with 15-ft. (4.57 m) line cord
- Includes 5-20P 20A 120V plug adapter
- 1U horizontal rackmount format installs in one rack space
- 12 NEMA 5-15/20R outlets
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
UPC Code	037332142504
PDU Type	Metered
INPUT	
PDU Input Voltage	120V



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	Single-phase 20A 120V service
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	2.4kW (120V) / 16A total capacity; 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15/20R
Output Nominal Voltage	120V
Overload Protection	20A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
Material of Construction	Metal
Minimum Required Rack Depth (cm)	24.13
Minimum Required Rack Depth (inches)	9.5
Outlets Measurement (Center to Center)	30.20mm
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	23.37 x 5.72 x 51.82
Shipping Dimensions (hwd / in.)	9.20 x 2.25 x 20.40
Shipping Weight (kg)	2.90
Shipping Weight (lbs.)	6.40
Unit Dimensions (hwd / cm)	4.45 x 44.5 x 11.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Weight (kg)	1.36
Unit Weight (lbs.)	3
ENVIRONMENTAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
TVSS Grounding	Back panel grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH20](#)