

1.5kW Single-Phase Metered PDU, 100-127V Outlets (8 5-15R), 5-15P, 15 ft. (4.57 m) Cord, 0U Vertical, 24 in.

MODEL NUMBER: PDUMV15-24



Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15-ft. (4.57 m) line cord
- 0U 24in / 61cm vertical rackmount format installs using no rack spaces
- 8 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Rear facing installation buttons can be relocated to the left or right surface of the PDU for rear, center or forward-facing outlet orientation in compatible racks
- Included nut and bolt mounting brackets support installation in non button-mount compatible racks, wallmount and raceway applications

Highlights

- Metered single phase 12A 100-127V 0U 24in / 61cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug
- 8 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

Package Includes

- PDUMV15 Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information

Specifications

OVERVIEW	
UPC Code	037332182852
PDU Type	Metered
INPUT	
PDU Input Voltage	100-127V



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	Single-phase 15A 100-127V service
Maximum Input Amps	12
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity; 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output Nominal Voltage	100-127V
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated safety cover
PHYSICAL	
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	4.83 x 13.72 x 68.83
Shipping Dimensions (hwd / in.)	1.90 x 5.40 x 27.10
Shipping Weight (kg)	1.54
Shipping Weight (lbs.)	3.40
Unit Dimensions (hwd / cm)	61 x 4.45 x 3.2
Unit Dimensions (hwd / in.)	24 x 1.75 x 1.25
Unit Weight (kg)	1.20
Unit Weight (lbs.)	2.65
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA) and CSA60950-1 (Canada), NOM (Mexico), Class A (Emissions), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMV15-24](#)