



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

12-Outlet Vertical Power Strip, 120V, 20A, Hardwired Input, 36 in.

MODEL NUMBER: **PS3612-20HW**



Highlights

- AC input hardwired via knockout on unit
- 12 outlets
- 20-amp capacity
- Ideal for applications requiring permanent installation

Package Includes

- PS3612-20HW
- Instruction manual

Description

Tripp Lite's PS3612-20HW Power Strip offers 20 amp multi-outlet AC power distribution in a convenient 36 inch hardwire cabinet. Includes knockout panels to accept 3/4 in. conduit fittings for hardwire installation and 12 output receptacles with 2.99 inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

INPUT/OUTPUT: Input: Hardwire access via knockout panels that accept 3/4 inch conduit fittings

Output: 12 Outlets total (2 NEMA 5-15/20R and 10 NEMA 5-15R)

ELECTRICAL: 120V AC, 50/60Hz, 20A (no circuit breaker)

FORMAT: 36 inch strip format

Features

- Versatile all-metal 36 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 12 outlets total: 2 NEMA 5-15/20R (20A) and 10 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332042385
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Electrical Service	20A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	Hard-wire
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(2) 5-15/20R; (10) 5-15R
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
Outlet Spacing	2.99 in.
PHYSICAL	
Color	Beige
Antimicrobial Coating	No
Housing Color	Beige
Integrated Keyhole Mounting Slots	No
Material of Construction	Metal
Outlets Measurement (Center to Center)	101.60mm
Receptacle Color	Beige
Shipping Dimensions (hwd / cm)	6.35 x 6.60 x 104.14
Shipping Dimensions (hwd / in.)	2.50 x 2.60 x 41.00
Shipping Weight (kg)	1.66
Shipping Weight (lbs.)	3.65
Unit Dimensions (hwd / cm)	91.44 x 3.8 x 3.8
Unit Dimensions (hwd / in.)	36 x 1.5 x 1.5
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	UL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS3612-20HW](#)