

Power It! 4-Outlet Power Strip, 10 ft. (3.05 m) Cord

MODEL NUMBER: **PS410**



Highlights

- 4 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 10-ft. (3.05 m) power cord
- ABS fire retardant plastic

Package Includes

- PS410 power strip
- Warranty information
- Instruction manual

Description

Tripp Lite's Power It! PS410 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 4 NEMA 5-15R outlets, 10-ft. (3.05 m) AC power cord.. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features ABS fire retardant plastic case to stand up to the most demanding environments, illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 4 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 10-ft. (3.05 m) AC power cord
- ABS fire retardant plastic case provides extra safety and durability
- UL certification

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332175540
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Material of Construction	ABS, Fire Retardant
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	30.48 x 3.81 x 14.99
Shipping Dimensions (hwd / in.)	12.00 x 1.50 x 5.90



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.64
Shipping Weight (lbs.)	1.40
Unit Dimensions (hwd / cm)	3 x 4.7 x 20.6
Unit Dimensions (hwd / in.)	1.2 x 1.85 x 8.1
Unit Weight (kg)	0.64
Unit Weight (lbs.)	1.4
STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS410](#)