



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite Waber Industrial Power Strip, 6-Outlet, 4 ft. (1.22 m) Cord

MODEL NUMBER: PS6



Highlights

- 6 outlets
- 4-ft. (1.22 m) cord
- 9.5-inch length
- Master on/off switch

Package Includes

- PS6 Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite PS6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles, 4-ft. (1.22 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the PS6 ideal for distributing alternate waveform UPS or generator power. Features power switch, circuit breaker and attractive gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Power switch
- 15A circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 4-ft. (1.22 m) AC line cord

Specifications

OVERVIEW

UPC Code

037332116123



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| INPUT | |
|------------------------------------|--|
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 4 |
| Input Cord Length (m) | 1.22 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (6) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (2) Yes |
| Outlet Orientation | Single row of 6 |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Master on/off switch with separate circuit breaker |
| PHYSICAL | |
| Color | Light Gray |
| Antimicrobial Coating | No |
| Power Cord Color | Light Gray |
| Housing Color | Gray |
| Integrated Keyhole Mounting Slots | Yes |
| Material of Construction | Plastic |
| Receptacle Color | Light gray |
| Shipping Dimensions (hwd / cm) | 26.92 x 5.08 x 9.14 |
| Shipping Dimensions (hwd / in.) | 10.60 x 2.00 x 3.60 |
| Shipping Weight (kg) | 0.38 |
| Shipping Weight (lbs.) | 0.83 |
| Unit Dimensions (hwd / cm) | 3.05 x 4.32 x 24.01 |
| Unit Dimensions (hwd / in.) | 1.20 x 1.70 x 9.45 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Unit Weight (kg) | 0.35 |
| Unit Weight (lbs.) | .77 |
| STANDARDS & COMPLIANCE | |
| Canada | cUL |
| UL1363 (Power Tap) | UL1363 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS6](#)