

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

## Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x 20A Hospital-Grade Outlets, 15 ft. (4.57 m) Cord

MODEL NUMBER: PS615HG20AOEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care areas.

### Description

The PS615HG20AOEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care areas, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-20P-HG hospital-grade plug and six NEMA 5-20R-HG hospital-grade outlets.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two resettable built-in 20A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. Locking safety covers are integrated to protect unused outlets from debris and damage.

Long 15-foot (4.6-meter) 20A AC power cord gives you flexibility to roll the equipment where it's most needed. Mounting tabs and flanges let you install the PS615HG20AOEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. All-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

### Features

**Power Distribution in Any Medical Facility** Ideal for operating rooms, administrative areas, patient-care areas, therapy rooms and imaging environments Attaches easily to IV poles, mobile carts, crash carts and mobile workstations 120V, 50/60 Hz power strip complies with UL 1363A specifications

**Exclusive, Patented Antimicrobial Protection** Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in

### Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Approved for use in patient-care areas when properly mounted
- Complies with UL 1363A specifications
- Features six NEMA 5-20R-HG hospital-grade outlets
- Features 15 ft. (4.6 m) cord with NEMA 5-20P-HG hospital-grade plug

### Package Includes

- PS615HG20AOEM UL 1363A Medical-Grade Power Strip with 6 20A Hospital-Grade Outlets
- Owner's Manual with maintenance requirements



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Versatile Medical-Grade Solution** Six NEMA 5-20R-HG hospital-grade outlets provide consistent power Long 15 ft. (4.6 m) 20A AC power cord with NEMA 5-20P-HG hospital-grade plug lets you move the components where power is most needed Rugged all-metal housing for long life in demanding environments

**Premium Safety Features** Dual resettable built-in 20A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff Integrated locking safety covers keep debris away from unused outlets

**Ready to Use Right from the Box** Mounting tabs and flanges let you install the unit on a wide variety of surfaces

## Specifications

OVERVIEW	
UPC Code	037332190680
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(6) 5-20R-HG
Circuit Breaker (amps)	20
Overload Protection	2 x 20amp breaker (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Color	White
Antimicrobial Coating	Yes
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between end tabs = 330.20mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	17.81 x 10.21 x 37.39
Shipping Dimensions (hwd / in.)	7.01 x 4.02 x 14.72
Shipping Weight (kg)	1.96
Shipping Weight (lbs.)	4.32
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 1.5
Unit Weight (kg)	1.02
Unit Weight (lbs.)	2.25
SPECIAL FEATURES	
Built-in Cable Management	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS615HG20AOEM](#)