



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Power It! 7-Outlet Power Strip, 12 ft. (3.66 m) Cord, Black Housing

MODEL NUMBER: **PS712B**



Highlights

- 7 outlets
- 12-ft. (3.66 m) power cord
- Illuminated on/off switch
- 15 amp circuit breaker
- Keyhole mounting slots

Package Includes

- PS712B Power Strip
- Instruction manual and warranty information

Description

Tripp Lite's PS712B power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. PS712B offers 7 total outlets, 12 foot cord. Attractive black housing with keyhole mounting slots and 1 designated transformer plug outlet. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket.

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/12-ft. (3.66 m) AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

Features

- 7 outlets / 12-ft. (3.66 m) cord
- Attractive black housing
- EMI/RFI noise filtering
- Can accommodate 1 transformer without blocking remaining outlets
- Keyhole supports for wall mounting

Specifications

OVERVIEW	
UPC Code	037332175212
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Power Cord Color	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 151mm; Distance between slot height = 24mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm
Receptacle Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	6.35 x 12.45 x 35.05
Shipping Dimensions (hwd / in.)	2.50 x 4.90 x 13.80
Shipping Weight (kg)	0.86
Shipping Weight (lbs.)	1.90
Unit Dimensions (hwd / cm)	3.35 x 5.21 x 29.69
Unit Dimensions (hwd / in.)	1.32 x 2.05 x 11.69
Unit Weight (kg)	0.80
Unit Weight (lbs.)	1.76
STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	RoHS
Approvals	Exceeds IEEE 587 category A&B specifications
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PS712B](#)