



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

NOT for Patient-Care Vicinity - UL 1363 1U Rackmount Power Strip with 12 Hospital-Grade Outlets, 15 ft. (4.57 m) Cord

MODEL NUMBER: RS1215-HG



Medical-grade rackmount power strip with long 15 ft. cord provides power distribution outside of patient-care vicinities.

Features

Versatile Power Distribution Outside of Patient-Care Vicinities

- Ideal for use in rackmount, wallmount and under-counter installation in administrative areas and other areas outside of patient-care vicinities
- Unfiltered electrical pass-through makes this strip ideal for distributing alternate waveform UPS or generator power in rack enclosures and network closets
- 120V, 50/60 Hz power strip complies with UL 1363 specifications

Versatile Medical-Grade Solution

- 12 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- 6 outlets are on front of unit, 6 are on rear of unit
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Resettable 15A circuit breaker protects against dangerous overloads
- Illuminated on/off switch has locking safety cover to prevent accidental shut-off

Ready to Use Right Out of the Box

- Detachable mounting flanges are configurable for versatile mounting orientation in a rack, on a wall or under a counter

Highlights

- Occupies 1U of space in a standard 19-in. rack
- Approved for use outside of patient-care vicinities
- Complies with UL 1363 specifications
- 15 ft. cord with NEMA 5-15P-HG hospital-grade plug
- 12 NEMA 5-15R-HG hospital-grade outlets

Package Includes

- RS1215-HG UL 1363 Medical-Grade Rackmount Power Strip with 12 15A Hospital-Grade Outlets and 15 ft. Cord
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332099365
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(12) 5-15R-HG
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	6 front / 6 rear
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Red illuminated 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Power Cord Color	Black
Form Factors Supported	1U rackmount, wallmount and undercounter installation supported
Housing Color	Black
Included Mounting Accessories	Rackmount flanges
Integrated Keyhole Mounting Slots	No
Material of Construction	Metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlets Measurement (Center to Center)	Distance between Front outlets = 83.35mm; Distance between Rear outlets = 165.1mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	23.88 x 5.72 x 51.56
Shipping Dimensions (hwd / in.)	9.40 x 2.25 x 20.30
Shipping Weight (kg)	2.77
Shipping Weight (lbs.)	6.10
Unit Dimensions (hwd / cm)	4.4 x 43.9 x 10.2
Unit Dimensions (hwd / in.)	1.75 x 17.3 x 4
Unit Weight (kg)	2.09
Unit Weight (lbs.)	4.6
SPECIAL FEATURES	
TVSS Grounding	Back panel nut and bolt grounding lug
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Canada	cUL (Series Number: AGIP120V6IPRM)
UL1363 (Power Tap)	UL1363 (UR status) (Series Number: AGIP120V6IPRM)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RS1215-HG](#)