

Protect It! Surge Suppressor

State of the art protection for every application



Model #: SUPER7TEL15

- ▶ 7 outlets / 15-ft. cord
- ▶ 2720 joule rating
- ▶ Modem/fax surge protection
- ▶ \$75,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

DESCRIPTION

Tripp Lite's SUPER7TEL15 surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. SUPER7TEL15 offers 7 total outlets, extra-long 15 foot cord with space-saving angled plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 2720 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. Lifetime warranty with \$75,000 connected equipment Insurance (USA & Canada Only).

PLUG / OUTLETS: Input: NEMA5-15P / Output: 7 NEMA5-15R / 15-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 3 transformer spaced outlets

SUPPRESSION: AC: 150V RMS Clamping / 2720 joules / 330V UL1449 Let-through Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

KEY BUYING POINTS

- 2720 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Extra long 15 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Lifetime warranty with \$75,000 Ultimate Lifetime connected equipment Insurance (USA & Canada Only)

TYPICAL APPLICATIONS

- Ideal for any desktop, network or home computing application requiring AC and dialup or DSL modem line protection

PACKAGE INCLUDES

- SUPER7TEL15 Surge Suppressor

- 6-ft. telephone cord
- Instrucion manual with warranty information

COMPLETE SPECIFICATIONS

SYSTEM OVERVIEW

System overview:	SUPER7TEL15 surge suppression strip includes 7 AC outlets, 15 foot AC cord, single line phone suppression, 2720 joule protection level, diagnostic LEDs, 3 dedicated tranformer outlets, lifetime warranty and \$75,000 connected equipment insurance
Voltage compatibility:	120 VAC
Frequency compatibility:	50/60 Hz

OUTPUT

Output volt amp capacity (amps):	15
Output watt capacity (watts):	1800
Outlet quantity / type:	7 NEMA 5-15R output receptacles
Outlet orientation:	Single row of 5, plus 2 side mounted outlets
Transformer accomodation:	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total

INPUT

Input connection type:	NEMA 5-15P
Input cord length (ft.):	15
Input cord length (m):	4.6
Input plug features:	Space-saving right angle input plug
Input cord gauge, type:	14 gauge, SJT
Recommended electrical service:	120V 15A

LEDS ALARMS & SWITCHES

Diagnostic LEDs:	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
Switches:	Two position on/off power switch

AC SURGE / NOISE SUPPRESSION

Protection modes:	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC suppression joule rating:	2720 joules
Clamping voltage (RMS):	150V
AC suppression response time:	< 1 ns
UL1499 let through rating:	330V - UL Verified
EMI / RFI filtering:	Up to 20 dB

DATALINE SURGE SUPPRESSION

TEL / Modem line protection:	Includes single line phone suppression via built-in RJ11 connectors, includes cable (260V clamping, 120 joules, center 2 wires protected)
-------------------------------------	---

PHYSICAL

Shipping weight (lbs):	2.4
Shipping weight (kg):	1.1
Unit weight (lbs):	2.2
Unit weight (kg):	1.0
Unit Dimensions (HWD/in):	10.25 x 2.75 x 1.5

Unit Dimensions (HWD/cm):	26 x 7 x 3.8
Shipping Dimensions (HWD/in):	15.25 x 6.25 x 3.5
Shipping Dimensions (HWD/cm):	38.7 x 15.9 x 8.9
Material of construction:	Plastic
Integrated keyhole mounting tabs:	Keyhole mounting tabs enable wall mounting
Housing color:	Attractive gray color scheme
AC line cord color:	Gray

CERTIFICATIONS

UL1449 1998 Rev. (AC Suppression):	UL1449
UL1363 (Power Tap):	UL1363
UL497A (Communications):	UL497A
FCC Part 68 (Communications):	FCC Part 68
cUL / CSA (Canada):	cUL
Industry Canada (Communications):	Industry Canada
Approvals:	Exceeds IEEE 587 category A&B specifications

WARRANTY

Product warranty:	Lifetime
Connected equipment insurance (USA and Canada Only):	Up to \$75,000

When you order today, you will receive the updated new version of these surge suppressors, however, they may be in packaging that still reflects the old specifications for joule and insurance amounts. In some cases the packaging you receive may have a sticker indicating these upgrades. This is simply due to an excess supply of existing packaging. Tripp Lite's ongoing commitment to having large quantities of product in stock at all times requires us to maintain large quantities of packaging. We are using this supply up as quickly as possible and are in the process of transitioning to new packaging. The timing will vary by product.

Please bear with us during this period of transition and rest assured that Protect It! Surge Suppressors are among the finest surge protection products available. If you want to know if your Protect It! Surge Suppressor offers the latest joule ratings and/or insurance amounts, refer to the date code on the back of your unit. If it was manufactured after 1/7/02 it is an upgraded version. For additional questions feel free to contact our Technical support hotline at (773) 869-1234 or email techsupport@tripplite.com.

*The policy of Tripp Lite is one of continuous improvement.
Specifications are subject to change without notice.
Therefore, your product may vary slightly from what is currently listed.*



Tripp Lite World Headquarters
1111 W. 35th Street
Chicago, IL 60609 USA

Customer Support
(773) 869-1234

© 2006 Tripp Lite. All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[S7TEL/15](#)