

SmartPro 120V 750VA 450W Line Interactive UPS, Tower, USB

MODEL NUMBER: **SMART750**



Description

Tripp Lite's SMART750 intelligent, line-interactive UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 16.2 minutes half load runtime and 5.6 minutes at full load during power failures. 750VA/450 watt power handling capability supports a variety of networking, telecom and various other application types, including the support of multiple network workstations. Includes a total of 6 UPS supported outlets. Supports remote monitoring of UPS and site power conditions via built-in USB monitoring port. PowerAlert UPS monitoring and unattended shutdown is available via free download. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level. Wall mountable with UPSWM wallmount bracket. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges.

Features

- 750VA/450 watt power handling capability supports a variety of networking, telecom and various other application types
- Built-in voltage regulation and battery support, plus complete AC line surge suppression prevents equipment damage, data loss and downtime
- Large internal batteries offer 16.2 minutes half load runtime and 5.6 minutes at full load during power failures
- Intelligent battery management system extends battery life
- Automatic Voltage Regulation (AVR) circuits with two boost and one voltage reduction level maintains usable 120V nominal output over an input voltage range of 75-147V
- Includes a total of 6 NEMA5-15R outlets
- Includes USB communications port for remote monitoring of UPS status and site power conditions

Highlights

- 750VA line interactive tower UPS system
- 120V nominal output during brownouts to 75V and overvoltages to 147V
- Front panel status LEDs with load and battery capacity level display
- USB communications port; Hot-swappable batteries
- NEMA 5-15P input; 6 NEMA 5-15R outlets

Package Includes

- SMART750 UPS System
- USB cable
- Instruction manual



- Communications port enables safe unattended shutdown without data loss during extended power failures
- Communications port supports messaging of UPS and line power status, including on-battery, low-battery, power-restored, AC line voltage, DC battery voltage and battery capacity
- Communications port supports timed inverter shutoff after unattended shutdown, activate self-test and 10-second reboot of connected equipment
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Battery replacement door allows on-site hot-swap battery replacement
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Notification of system status via 5 LEDs and multi-function audible alarms
- Wall mountable with UPSWM wallmount bracket
- Cold start capability enables UPS turn-on in battery mode during blackout conditions

Specifications

OVERVIEW	
UPC Code	037332139610
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	4.4A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	750
Output Watt Capacity (Watts)	450
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz

3 / 5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	300
Primary UPS Width (mm)	183
Shipping Dimensions (hwd / cm)	38.86 x 27.18 x 26.92
Shipping Dimensions (hwd / in.)	15.30 x 10.70 x 10.60
Shipping Weight (kg)	10.80
Shipping Weight (lbs.)	23.80
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	29.97 x 18.29 x 19.05
UPS Power Module Dimensions (hwd, in.)	11.8 x 7.2 x 7.5
UPS Power Module Weight (kg)	10.43
UPS Power Module Weight (lbs.)	23
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	134
Battery Mode BTU / Hr. (Full Load)	568
AC Mode Efficiency Rating (100% Load)	92%
COMMUNICATIONS	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	USB
LINE / BATTERY TRANSFER	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART750](#)