



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Power strips used within the patient care vicinity may be permanently attached so that it is only removable with a tool. Choose the PSCLAMP for a safe and secure mounting solution.

Safe-IT UL 60601-1 Medical-Grade Power Strip for Patient-Care Vicinity, Surge Protection, 4x Hospital-Grade Outlets, 6 ft. Cord

MODEL NUMBER: SPS406HGULTRA



Full 60601-1 compliance and agency listing, surge protection, integrated locking safety covers and a 6 ft. cord make this medical-grade power strip ideal for standalone use in areas inside and outside patient-care vicinities.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for standalone use in all patient-care vicinities, therapy rooms, imaging environments, laboratories and administrative areas 120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications Automatic single-fault protection Tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 Canadian standards Patent # 7,375,939 & 8,339,759

Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 6 ft. power cord with NEMA 5-15P-HG plug provides ample reach to the power source Rugged all-metal housing for long life in demanding environments

Premium Safety Features 1410 joules of surge suppression protect against dangerous power spikes Integrated locking outlet safety covers block access to unused outlets Built-in 15A resettable circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off LED indicates power is present and surge-protected

Ready to Use Right Out of the Box Built-in mounting slots and flanges for easy installation on a variety of surfaces

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Approved for standalone use in all patient-care vicinities
- Listed to UL 60601-1 and UL 60950-1 specifications
- 1410 joules of surge suppression
- Automatic single-fault detection for added patient protection

Package Includes

- SPS406HGULTRA UL 60601-1 Medical-Grade Power Strip
- Owner's manual

Specifications

OVERVIEW

UPC Code

037332194091



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
LED Indicators	Proper wiring and surge protection working
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1410
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	Yes
Power Cord Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Housing Color	White
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Material of Construction	Metal
Receptacle Color	White
Shipping Dimensions (hwd / cm)	6.10 x 14.73 x 36.58
Shipping Dimensions (hwd / in.)	2.40 x 5.80 x 14.40
Shipping Weight (kg)	1.18
Shipping Weight (lbs.)	2.60
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.20
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	TUV tested and Listed to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
Patented	Patent# 7,375,939; Patent# 8,339,759
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SPS406HGULTRA](#)