

25U SmartRack 4-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST25



Description

Tripp Lite's 25U 4-Post Open Frame Rack helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST25 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 25U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1000 lbs (453.6 kgs). The SR4POST25 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST25 provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POST25 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000 lbs (453.6 kgs) of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Highlights

- 25U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST25
- Installation hardware
- 32x pieces of M6 cage nuts, screws, and washers for equipment mounting
- 18x Cable management hooks
- Owner's manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332157942
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Minimum Device Depth (cm)	55.88
Minimum Device Depth (in.)	22
Minimum Device Depth (mm)	559
Rack Height	25U
Shipping Dimensions (hwd / cm)	16.51 x 11.51 x 136.40
Shipping Dimensions (hwd / in.)	6.50 x 4.53 x 53.70
Shipping Weight (kg)	22.23
Shipping Weight (lbs.)	49.00
Unit Dimensions (hwd / cm)	125.2 x 51.3 x 55.9~91.44 (depth adjustable)
Unit Dimensions (hwd / in.)	49.3 x 20.2 x 22-36
Unit Weight (kg)	20.41
Unit Weight (lbs.)	45
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Rack Depth	Standard
Number of Vertical Mounting Rails	4
SPECIAL FEATURES	
Grounding Lug	Included screws, nuts, and washers secure user-supplied grounding wire to Front or Back frames
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	5-year limited warranty
----------------------------------------	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SR4POST25](#)