

In-Row Cooler for Server Racks - 33,000 BTU, 208/240V, 42U

MODEL NUMBER: SRCOOL33K



Self-contained rack cooling system provides up to 33,000 BTU of close-coupled cooling to high-density IT equipment.

Features

Get Highly Efficient, Reliable Cooling in a 42U Rack Form Factor The harder your data center, network closet or server room works, the more it heats up, leading to inefficient operation, weakened performance and raised cooling costs. To help prevent equipment shutdowns, malfunctions and failures caused by overheating and temperature fluctuations, the SmartRack® SRCOOL33K provides a close-coupled cooling solution in a 42U rack form factor that reduces energy use, lowers operating costs and simplifies installation.

Completely Self-Contained for Simplified and Less Expensive Installation and Maintenance The zero-maintenance SRCOOL33K with its intuitive LCD interface is easy to install and operate. You and your IT staff can install it yourself. No costly startup service, electrician or HVAC contractor is needed. A built-in evaporator eliminates condensation through the exhaust air stream, so no costly floor drain, water collection tank, external condenser, refrigerant piping, ductwork or plumbing is required.

Advanced Network Monitoring Keeps You in Touch 24/7 The pre-installed Java-free HTML5-based WEBCARDLX interface enables full remote monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

Energy-Saving Features Meant to Save You Money A row-based airflow path maximizes hot-aisle/cold-aisle efficiency and cooling predictability by delivering cold air high in the cold aisle and removing hot air in the hot aisle. The SRCOOL33K promotes temperature uniformity from 1U to 42U, allowing your equipment to perform at its peak and reduce power consumption and operating costs, and features an AC-driven rotary compressor.

One-Year Warranty and Environmentally Responsible Design The SRCOOL33K comes with a one-year warranty. It's manufactured in compliance with strict RoHS specifications and uses eco-friendly R410a refrigerant, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- 33,000 BTU (9.7kW) of cooling power in self-contained, row-based, zero-maintenance unit
- Needs no costly electrician or HVAC contractor—can be fully installed by IT staff
- Expels condensation through exhaust air system—no floor drain or water collection tank required
- 10-ft. (3.05 m) cord with NEMA L6-30P plug connects to 208/240V outlet
- Supports remote management 24/7 via pre-installed WEBCARDLX network interface

Applications

- Primary cooling of high-density equipment in a small server room, wiring closet or data center

Package Includes

- SRCOOL33K SmartRack Energy-Saving, Row-Based Server Rack Cooling Unit - 33,000 BTU, 208/240V
- Flexible air ducts
- Hot-exhaust removal tube
- Unloading ramps
- Unpacking guide
- Installation manual
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332172280
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Maximum Input Amps	17.9
Input Connection Type	L6-30P Input Cordset
Input Frequency	60 Hz
Maximum Surge Amps	23
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
COOLING	
Cooling Type	Active
Airflow	1200 CFM
Equivalent Room Size	1,250 sq. ft. (115 sq. m)
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Multi-line LCD control panel
PHYSICAL	
Color	Black
Material of Construction	Aluminium, Steel
Shipping Dimensions (hwd / cm)	214.38 x 65.02 x 114.05
Shipping Dimensions (hwd / in.)	84.40 x 25.60 x 44.90
Shipping Weight (kg)	285.76
Shipping Weight (lbs.)	630.00
Unit Dimensions (hwd / cm)	199.14 x 59.94 x 108.46
Unit Dimensions (hwd / in.)	78.4 x 23.6 x 42.7
Unit Weight (kg)	253.10
Unit Weight (lbs.)	558.00
ENVIRONMENTAL	
Cooling Capacity	33,000 BTU / 9.7 kW
SPECIAL FEATURES	
Dehumidifier	3.35 L/HR



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Compressor Type	AC ROTARY
Refrigerant	R410a (Environmentally friendly, Non ozone depleting)
Refrigerant Amount	2.25 KG
Amp Draw Nominal	Variable
Sound Level (Noise)	60 dB
Air Exhaust Tube Length	98 inches
Air Exhaust Tube Diameter	9.84 inches
STANDARDS & COMPLIANCE	
Certifications	Tested to UL484; CSA, RoHS, FCC Class A
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRCOOL33K](#)