

## Power It! 10-Outlet Power Strip, 15 ft. (4.57 m) Cord

MODEL NUMBER: TLM1015NC



### Highlights

- 10 outlets spaced to accommodate transformers
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Heavy-duty metal case
- Keyhole slots on removable mounting brackets

### Package Includes

- TLM1015NC power strip
- Warranty information
- Instruction manual

### Description

Tripp Lite's Power It! TLM1015NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R outlets spaced to accommodate transformers, 15-ft. (4.57 m) AC power cord and keyhole slots on removable mounting brackets. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features heavy-duty metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 10 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 10 NEMA 5-15R outlets spaced to accommodate transformers
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots on removable brackets provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-ft. (4.57 m) AC power cord
- Heavy-duty metal case provides maximum safety and durability
- UL certification

## Specifications



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332136107
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(5) Yes
Outlet Orientation	10 outlets arranged in 2 rows and spaced to accommodate transformers
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Included Mounting Accessories	Keyhole slots on removable mounting brackets
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between end tabs = 462.30mm
Material of Construction	Metal



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Outlets Measurement (Center to Center)	Distance between horizontal outlets = 71.45mm; Distance between vertical outlets = 38.90mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	6.60 x 23.11 x 51.31
Shipping Dimensions (hwd / in.)	2.60 x 9.10 x 20.20
Shipping Weight (kg)	2.31
Shipping Weight (lbs.)	5.10
Unit Dimensions (hwd / cm)	44.5 x 10.2 x 5.7
Unit Dimensions (hwd / in.)	17.5 x 4 x 2.25
Unit Weight (kg)	2.09
Unit Weight (lbs.)	4.6
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLM1015NC](#)