

Protect It! 4-Outlet Home Computer Surge Protector Strip, 4 ft. (1.22 m) Cord, 450 Joules

MODEL NUMBER: TLP404



Highlights

- 4 outlets / 4-ft. (1.22 m) cord
- 450 joule rating

Package Includes

- TLP404 surge suppressor
- Instruction manual with warranty information

Description

Tripp Lite's TLP404 offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP404 offers 4 total outlets, 4-ft. (1.22 m) cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 450 joules shields equipment from surges and line noise. Attractive light gray suppressor housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories. \$1,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 4 NEMA5-15R/4-ft. (1.22 m) AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/450 joules/500V UL1449 3rd Edition

Features

- 4 outlets
- 4-ft. (1.22 m) cord
- Surge suppression rating: 450 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LED confirms surge protection status
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 2 total transformers
- Keyhole supports for wall mounting
- Non-Lighted power switch
- \$1,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)



- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332119131
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	22500
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	4
Right-Angle Plug	No
Input Cord Length (m)	1.22
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	



AC Suppression Joule Rating	450
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500V - UL Verified
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 57.5mm; Distance between slot height = 26mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	28.6mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	30.23 x 5.08 x 12.70
Shipping Dimensions (hwd / in.)	11.90 x 2.00 x 5.00
Shipping Weight (kg)	0.40
Shipping Weight (lbs.)	0.88
Unit Dimensions (hwd / cm)	3 x 4.7 x 20.6
Unit Dimensions (hwd / in.)	1.2 x 1.85 x 8.1
Unit Weight (kg)	0.45
Unit Weight (lbs.)	1
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL



Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$1,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP404](#)