



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Protect It! 230V Surge Protector with 6 French/Belgian Outlets, 2M Cord, 1140 Joules, French plug

MODEL NUMBER: TLP61F



Highlights

- 6 safety outlet covers
- 2 m cord
- "Protected" LED
- 1140 joule rating

Package Includes

- TLP61F surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP61F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP61F offers 6 French Type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP61F offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 6 French Type E outlets protects computers and peripherals
- 2 m cord with French plug
- Protected LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145444
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Plug Type	French
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(6) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(3) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	No
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	46.23 x 4.44 x 12.19
Shipping Dimensions (hwd / in.)	18.20 x 1.75 x 4.80
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
Unit Dimensions (hwd / cm)	40.64 x 5.89 x 4.45
Unit Dimensions (hwd / in.)	16 x 2.32 x 1.75



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.2
SPECIAL FEATURES	
Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP61F](#)