

Protect It! 6-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Ethernet Protection, Safety Covers

MODEL NUMBER: TLP66NET



Highlights

- 6 outlets / 6-ft cord
- 1080 joule rating
- Ethernet surge protection

Package Includes

- TLP66NET
- 6-ft. network cable
- Instruction manual with warranty information

Description

Tripp Lite's TLP66NET surge suppressor has 6 outlets, a 6-ft. cord and diagnostic LEDs. The unit has a surge suppression rating of 1080 joules to handle the strongest surges. Built-in RJ45 jacks prevent surges from damaging your network equipment (6-ft network cable included). \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets with integrated child safety covers
- 6ft cord
- Built-in RJ45 jacks prevent surges from damaging your network equipment (6ft. network cable included)
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- Can accommodate up to 2 transformers without blocking remaining outlets
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Lighted power switch
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332159700
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Block style with two rows of 3 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400v
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Color (AC Line Cord)	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	119mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5; Distance between standard outlet and transformer outlet = 48.5mm
Receptacle Color	Gray
Shipping Dimensions (hwd / cm)	28.19 x 5.08 x 18.29
Shipping Dimensions (hwd / in.)	11.10 x 2.00 x 7.20
Shipping Weight (kg)	0.86
Shipping Weight (lbs.)	1.90
Unit Dimensions (hwd / cm)	3.81 x 10.74 x 21.06
Unit Dimensions (hwd / in.)	1.5 x 4.23 x 8.29
Unit Weight (kg)	0.60
Unit Weight (lbs.)	1.32
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
Industry Canada (Communications)	Industry Canada
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP66NET](#)