

## Protect It! 7-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1080 Joules, Modem/Fax Protection, Black Housing

MODEL NUMBER: TLP76RBTEL



### Highlights

- 7 outlets (6 right-angle outlets and 1 designated transformer outlet)
- 6-ft. (1.83 m) cord
- 1080 joule rating
- Modem/fax surge protection

### Package Includes

- TLP76RBTEL Surge Suppressor

### Description

Tripp Lite's TLP76RBTEL surge suppressor offers complete AC and phone line surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP76RBTEL offers 7 total outlets (6 at right angle and 1 designated transformer plug outlet), 6-ft. (1.83 m) cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive black housing with keyhole mounting tabs offering convenient protection of desktop computer equipment and accessories. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/4-ft. (1.22 m) AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/540 joules/400V UL1449 Let-through

### Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 total AC outlets (6 right angle and 1 transformer plug outlet)
- 6-ft. (1.83 m) AC line cable
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more
- Attractive black housing
- Lighted on/off switch with integrated circuit breaker for overload protection of all outlets



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Diagnostic LED confirms surge suppression status
- Integrated keyhole slots provide convenient wall/desk mounting
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW                           |                 |
|------------------------------------|-----------------|
| UPC Code                           | 037332175649    |
| INPUT                              |                 |
| Nominal Input Voltage(s) Supported | 120V AC         |
| Recommended Electrical Service     | 120V (110-125V) |
| Input Cord Gauge Type              | 14 gauge; SJT   |
| Voltage Compatibility (VAC)        | 120             |
| Maximum Surge Amps                 | 36000           |
| Input Plug Type                    | NEMA 5-15P      |
| Input Cord Length (ft.)            | 6               |
| Right-Angle Plug                   | No              |
| Input Cord Length (m)              | 1.83            |
| Integrated Cord Clip               | No              |
| OUTPUT                             |                 |
| Frequency Compatibility            | 60 Hz           |
| Output (Watts)                     | 1800            |
| Output Receptacles                 | (7) 5-15R       |
| Circuit Breaker (amps)             | 15              |
| Transformer Accommodation          | (4) Yes         |
| Outlet Orientation                 | Single row      |
| Right-Angle Outlets                | Yes             |
| USER INTERFACE, ALERTS & CONTROLS  |                 |
| Diagnostic LED(s)                  | Yes             |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                                      |                                                                                    |
|------------------------------------------------------|------------------------------------------------------------------------------------|
| Switches                                             | Combination AC circuit breaker and 2 position on/off power switch                  |
| Diagnostic LED Details                               | Built-in LED confirms suppressor "protection present" (green) status               |
| <b>SURGE / NOISE SUPPRESSION</b>                     |                                                                                    |
| AC Suppression Joule Rating                          | 1080                                                                               |
| AC Suppression Response Time                         | < 1 ns                                                                             |
| Protection Modes                                     | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS)                               | 150                                                                                |
| UL1449 Let Through Rating                            | 400V                                                                               |
| Automatic Shut-Off                                   | Yes                                                                                |
| <b>DATALINE SURGE SUPPRESSION</b>                    |                                                                                    |
| Telephone/DSL Protection                             | Yes                                                                                |
| Cable (Coax) Protection                              | No                                                                                 |
| Network (Ethernet) Protection                        | No                                                                                 |
| <b>PHYSICAL</b>                                      |                                                                                    |
| Antimicrobial Coating                                | No                                                                                 |
| Power Cord Color                                     | Black                                                                              |
| Housing Color                                        | Black                                                                              |
| Integrated Keyhole Mounting Slots                    | Yes                                                                                |
| Keyhole Slot Mounting Measurement (Center to Center) | 207mm                                                                              |
| Material of Construction                             | Plastic                                                                            |
| Outlets Measurement (Center to Center)               | 28.5mm                                                                             |
| Receptacle Color                                     | Black                                                                              |
| Shipping Dimensions (hwd / cm)                       | 35.56 x 5.08 x 12.19                                                               |
| Shipping Dimensions (hwd / in.)                      | 14.00 x 2.00 x 4.80                                                                |
| Shipping Weight (kg)                                 | 0.64                                                                               |
| Shipping Weight (lbs.)                               | 1.41                                                                               |
| Unit Dimensions (hwd / cm)                           | 3.35 x 5.21 x 31.78                                                                |
| Unit Dimensions (hwd / in.)                          | 1.32 x 2.05 x 12.51                                                                |
| Unit Weight (kg)                                     | 0.55                                                                               |
| Unit Weight (lbs.)                                   | 1.21                                                                               |
| <b>SPECIAL FEATURES</b>                              |                                                                                    |
| Rotatable Outlets                                    | No                                                                                 |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| STANDARDS & COMPLIANCE                                     |                                                                                                                       |
|------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Canada                                                     | cUL                                                                                                                   |
| Approvals                                                  | Exceeds IEEE 587 category A&B specifications                                                                          |
| UL1449 3rd Edition (AC Suppression)                        | UL1449 3rd Edition                                                                                                    |
| UL1363 (Power Tap)                                         | UL1363                                                                                                                |
| WARRANTY                                                   |                                                                                                                       |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                                                                                             |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP76RBTEL](#)