



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## TouchMaster 6-Outlet Under-Monitor Surge Protector, 6 ft. (1.83 m) Cord, 1440 Joules, Tel/Modem Protection

MODEL NUMBER: **TMC-6**



### Highlights

- 6 outlets / 6-ft. cord
- 1440 joule rating
- Tel/modem surge protection
- Individual switches

### Package Includes

- TOUCHMASTER COMPACT surge suppressor
- 6-ft. (1.83 m) phone cord
- Instruction manual and warranty information

### Description

Tripp Lite's TOUCHMASTER COMPACT surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TOUCHMASTER COMPACT offers 6 total outlets, 6-ft. (1.83 m) cord and LEDs to warn of power and wiring problems. Heavy grade AC suppression rated at 1440 joules shields equipment from surges and line noise. Attractive, slim design is perfect for use under desktop computer monitors or notebook computers. Individual switches offer power control over connected equipment. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. (1.83 m) AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Slim, compact design perfect for use under desktop monitors and notebook computers

SUPPRESSION: AC: 150V RMS Clamping/1440 joules/400V UL1449 3rd Edition

### Features

- 6 outlets
- 6-ft. (1.83 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6-ft. (1.83 m) telephone cord included
- Surge suppression rating: 1440 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Diagnostic LEDs confirm suppressor "protection present" (green), "grounded" (red) status and "power on" (green)
- Always-on outlet provides power for equipment you always need on, even when the "master" switch is off
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Allows for the computer to be controlled by the "master" switch and other outlets to be controlled either the "master" switch or corresponding switch on the front panel
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

OVERVIEW	
UPC Code	037332119117
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	84000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Diagnostic LED(s)	Yes
Switches	Includes 5 front panel AC power switches. 4 switches control individual outlets and 1 serves as a main power switch that controls all but the one marked "unswitched" on the back panel
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1440
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Power Cord Color	Black
Form Factors Supported	Supports under monitor placement as a power control center for an entire PC system with peripherals
Housing Color	Black
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 31.24 x 33.78
Shipping Dimensions (hwd / in.)	2.00 x 12.30 x 13.30
Shipping Weight (kg)	1.50
Shipping Weight (lbs.)	3.30
Unit Dimensions (hwd / cm)	4.45 x 29.21 x 30.48
Unit Dimensions (hwd / in.)	1.75 x 11.5 x 12
Unit Weight (kg)	1.27
Unit Weight (lbs.)	2.8



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

SPECIAL FEATURES	
Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TMC-6](#)