


Protect It! 6-Outlet Super Surge Alert Protector, 6 ft. (1.83 m) Cord, 2420 Joules

MODEL NUMBER: TR-6



Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 2420 joule rating

Package Includes

- TR-6 Surge Suppressor
- Child Safety Covers
- Color-coded cord identifiers
- Instruction manual and Warranty information

Description

The TR-6 Surge Suppressor from Tripp Lite has 6 outlets and a 6-ft. (1.83 m) cord with a space-saving right-angle plug. The unit has 2420 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). The Super Surge Alert comes with child safety covers and color-coded cord identifiers.

Features

- 6 outlets with child safety covers
- 6-ft. (1.83 m) cord with space-saving right-angle plug
- Surge energy absorption: 2420 joules; 78,500 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, line fault & protection present
- EMI/RFI noise filtering
- Logical outlet spacing accommodates transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332010315
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	97000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2420
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	78,500 amps
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	88.8mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 44.20mm; Distance between vertical outlets = 39mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	30.48 x 6.10 x 15.49
Shipping Dimensions (hwd / in.)	12.00 x 2.40 x 6.10
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / cm)	4.45 x 8.9 x 24.13
Unit Dimensions (hwd / in.)	1.75 x 3.5 x 9.5
Unit Weight (kg)	0.73
Unit Weight (lbs.)	1.6
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TR-6](#)