

## Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 13A, 125V, 16 AWG, 3 ft., Clear Plugs

MODEL NUMBER: P006-003-HG13CL



Connects your PC, mobile cart or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

### Features

#### Hospital-Grade Power Cable is a Safe Solution for Medical Facilities

This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

#### Designed and Tested to Strict Hospital-Grade Standards

Both fully molded ends are clear, so you can inspect their internal connections at a glance. This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

### Highlights

- Fully molded clear plugs allow visual inspection of internal construction to ensure safety
- Recommended for connecting devices to power outlets outside patient-care vicinities
- 3 ft. length allows flexibility in placing devices, while avoiding cable clutter
- Hospital-grade power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

### Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 3 ft. away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P006-003-HG13CL Hospital-Grade Power Cord, NEMA 5-15P to C13, 3 ft., Clear Plugs

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332193247
Country/Region	North America
Power Cord Application	PC; Monitor; Server; Mobile Cart
<b>INPUT</b>	
Maximum Input Amps	13
Cable Length (ft.)	3
Cable Length (m)	0.9
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Power Cord Jacket Type	SJT
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
Shipping Dimensions (hwd / in.)	7.00 x 9.90 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 25.15 x 1.27
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
Color	Black
Number of Conductors	3
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>CERTIFICATIONS</b>	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 49, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P006-003-HG13CL](#)