

## USB-C to DisplayPort Cable, 4K @ 60Hz, Thunderbolt 3, 6 ft.

MODEL NUMBER: **U444-006-DP**



USB-C to DisplayPort adapter connects your DP monitor to the USB-C or Thunderbolt 3 port on your Chromebook or MacBook.

### Features

#### Connects a DisplayPort Display to Your USB-C or Thunderbolt 3 Device

This USB-C to DisplayPort 4K cable helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DisplayPort-enabled monitor or projector. It's ideal for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 4K.

#### Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video Signals

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

#### Transmits Crystal-Clear 4K Video and Digital Audio

This six-foot cable supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, 36-bit Deep Color (12 bits per channel) and per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR). It also supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps. The cable is backward compatible with non-4K displays, so you can use a 1080p monitor if one is available.

#### Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

#### Premium Construction for Premium Performance

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief reduces stress and helps the cable and connectors move freely without cracking.

#### Ready to Use Right Out of the Package

The plug-and-play USB-C to DisplayPort adapter requires no software, drivers or external power and works with both Windows and Mac operating systems. Just plug the USB-C end into your computer's USB-C or Thunderbolt 3 port, and plug the DisplayPort end into the display's input port for immediate satisfaction. The six-foot cable fits easily into a briefcase or laptop bag for connecting on the go.

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

### Applications

- Play 4K video from your laptop, Chromebook or MacBook on a large-screen monitor
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DisplayPort input

### Package Includes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

### 3-Year Warranty and Environmentally Responsible Design

The U444-006-DP comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

- U444-006-DP USB-C to DisplayPort Cable, 4K @ 60Hz, Thunderbolt 3, 6 ft.

## Specifications

| OVERVIEW                        |                                                              |
|---------------------------------|--------------------------------------------------------------|
| UPC Code                        | 037332210388                                                 |
| Technology                      | DisplayPort (all types); USB 3.1 (Gen 1); USB (all versions) |
| INPUT                           |                                                              |
| Cable Length (ft.)              | 6                                                            |
| Bus Powered                     | Yes                                                          |
| PHYSICAL                        |                                                              |
| Shipping Dimensions (hwd / in.) | 0.500 x 7.000 x 9.000                                        |
| Shipping Weight (lbs.)          | 0.4000                                                       |
| Unit Packaging Type             | Polybag                                                      |
| Unit Weight (lbs.)              | 0.23                                                         |
| Unit Weight (kg)                | 0.10                                                         |
| Material of Construction        | PVC and ABS                                                  |
| Color                           | Black                                                        |
| Cable Jacket Rating             | VW-1                                                         |
| ENVIRONMENTAL                   |                                                              |
| Operating Temperature Range     | 32 to 113 F (0 to 45 C)                                      |
| Storage Temperature Range       | 14 to 158 F (-10 to 70 C)                                    |
| BTUs                            | 2.1 BTU/Hr                                                   |
| Power Consumption (Watts)       | 0.6                                                          |
| Operating Humidity Range        | 10% to 85% RH, non-condensing                                |
| Storage Humidity Range          | 5% to 90% RH, non-condensing                                 |
| CONNECTIONS                     |                                                              |
| Side A - Connector 1            | USB C (MALE)                                                 |
| Side B - Connector 1            | DISPLAYPORT (MALE)                                           |
| Connector Plating               | Gold                                                         |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| FEATURES & SPECIFICATIONS           |                                                      |
|-------------------------------------|------------------------------------------------------|
| Max Supported Video Resolution      | 3840 x 2160 @ 60Hz                                   |
| Displayport Specification           | 1.2                                                  |
| HDCP Specification                  | 1.3                                                  |
| USB Specification                   | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required                     | No                                                   |
| CERTIFICATIONS                      |                                                      |
| Certifications                      | CE, FCC, ROHS, REACH                                 |
| WARRANTY                            |                                                      |
| Product Warranty Period (Worldwide) | 3-year limited warranty                              |

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-006-DP](#)