

- Singlemode can support 40GBASE-PLR4/100GBASE-PSM4 in applicable parallel optics networks

## MTP/MPO (APC) Singlemode Patch Cable (F/F), 12 Fiber, 40/100 GbE, QSFP+ 40GBASE-PLR4, Plenum, Push/Pull Tab, Yellow, 1 m (3.3 ft.)

MODEL NUMBER: **N390-01M-12-AP**



Premium 8.3/125 singlemode fiber optic cabling for transmitting 40/100 Gb data and voice signals over long distances. Designed for enterprise applications in wiring closets, telecom rooms and data centers.

### Description

The N390-01M-12-AP MTP/MPO Singlemode Patch Cable (F/F) supports 40/100 Gb Ethernet speeds and is designed for QSFP+ applications in enterprise installations in wiring closets, telecom rooms and data centers. With two female MTP/MPO connectors, this singlemode fiber optic cable with plenum-rated jacket is recommended for connecting switches, hubs, routers and other high-speed network components in ceilings, walls and ducts.

The 12-fiber MTP/MPO connectors are about the same size as SC connectors, but are 12 times denser, freeing up rack space for other cables. The APC connectors are angled to prevent infrared light entering the fiber from bouncing back into the laser. The N390-01M-12-AP is tested for low insertion loss and back reflection on every connector and attenuation loss that meets or exceeds current standards.

The N390-01M-12-AP is colored yellow for instant identification in a crowded switch or patch panel as a singlemode cable. Push/pull tab connectors are easily accessible in high-density data center environments and make the plug-and-play cable easy to install and remove with one hand.

### Features

#### 8.3/125 Rated Singlemode Cable for 40/100 Gb Ethernet Applications

- Designed for enterprise applications in wiring closets, telecom rooms and data centers
- Recommended for QSFP+ applications in enterprise installations
- Plenum-rated jacket suited for ceilings, walls and ducts

### Highlights

- Push/pull tab connectors easily install/remove with one hand
- 12-fiber MTP/MPO connectors with 12x density of SC connectors
- 100% tested for low insertion loss and back reflection
- Angled APC connectors protect laser against destabilization
- Yellow color for easy singlemode identification

### Package Includes

- N390-01M-12-AP MTP/MPO Singlemode Patch Cable (F/F), Yellow, 1 m



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Yellow-colored for identification as a singlemode cable

#### MTP/MPO APC Connectors with Push/Pull Tabs

- 12-fiber female connectors 12 times denser than SC connectors
- APC connector angled to prevent light from reflecting back into laser
- Push/pull tabs easy to install and remove with one hand
- 100% tested for low insertion loss and back reflection

## Specifications

OVERVIEW	
UPC Code	037332205360
Technology	MTP/MPO; Singlemode
INPUT	
Cable Length (ft.)	3.3
Cable Length (m)	1
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.0500
Shipping Weight (kg)	0.02
Color	Yellow
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
CONNECTIONS	
Side A - Connector 1	12-STRAND MTP (FEMALE)
Side B - Connector 1	12-STRAND MTP (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N390-01M-12-AP](#)