

Singlemode can support 40GBASE-PLR4 / 100GBASE-PSM4 in applicable parallel optics networks

MTP/MPO (APC) to 8xLC (UPC) Singlemode Breakout Patch Cable, 40/100 GbE, QSFP+ 40GBASE-PLR4, Plenum, Yellow, 1 m (3.3 ft.)

MODEL NUMBER: N390-01M-8LC-AP



Premium 8.3/125 singlemode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density fiber patching between data center MDFs and IDF's in enterprise installations.

Description

The N390-01M-8LC-AP MTP/MPO to 8xLC Singlemode Breakout Patch Cable supports 40/100 Gb Ethernet speeds and is designed for high-density fiber patching between data center MDFs (main distribution frames) and IDF's (intermediate distribution frames) in enterprise installations. It's optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks. Its plenum-rated jacket makes it ideal for connecting switches, hubs, routers and other high-speed network components in ceilings, walls and ducts.

The 12-fiber MTP/MPO connector is about the same size as an SC connector, but is 12 times denser, freeing up rack space for other cables. The APC connector is angled to prevent infrared light entering the fiber from bouncing back into the laser. The N390-01M-8LC-AP is tested for low insertion loss and back reflection on every connector and attenuation loss that meets or exceeds current standards.

The N390-01M-8LC-AP uses eight fibers to fully transmit 40GBASE-PLR4 with four fibers transmitting at 10 Gbps in each direction. Its slim, space-saving uniboot design allows easier cable management. The LC UPC connector's premium-grade ceramic ferrule is designed for fast applications of 10 GbE and higher.

The singlemode cable is colored yellow for instant identification in a crowded switch or patch panel. Push/pull tab connectors are easily accessible in high-density data center environments and make the plug-and-play cable easy to install and remove with one hand.

Features

Highlights

- Push/pull tab connectors install/remove with one hand
- 12-fiber MTP/MPO connectors with 12x density of SC connectors
- Slim space-saving uniboot design for easy cable management
- Angled APC connectors protect laser against destabilization
- Yellow color for quick singlemode identification

Package Includes

- N390-01M-8LC-AP MTP/MPO to 8xLC Singlemode Breakout Patch Cable, Yellow, 1 m



8.3/125 Rated Singlemode Cable for 40/100 Gb Ethernet Applications

- Designed for high-density fiber patching between data center MDFs and IDF's in enterprise installations
- Optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks
- Plenum-rated jacket suited for ceilings, walls and ducts
- Yellow-colored for identification as a singlemode cable

MTP/MPO APC and LC Duplex UPC Connectors with Push/Pull Tabs

- MTP/MPO female connector and 8 LC duplex male connectors—no splicing required
- 12-fiber MTP/MPO connector 12 times denser than SC connector
- APC connector angled to prevent light from reflecting back into laser
- UPC connector with premium-grade ceramic ferrule for 10 GbE and faster applications
- Push/pull tabs easy to install and remove with one hand

Error-Free Signal Transfer

- Fully transmits 40GBASE-PLR4 with 4 fibers transmitting at 10 Gbps in each direction
- 100% tested for low insertion loss and back reflection
- Slim, space-saving uniboot design easier to manage in crowded applications

Specifications

OVERVIEW	
UPC Code	037332205414
Technology	MTP/MPO; Singlemode
INPUT	
Cable Length (ft.)	3.3
Cable Length (m)	1
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.1400
Shipping Weight (kg)	0.06
Color	Yellow
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
CONNECTIONS	
Side A - Connector 1	12-STRAND MTP (FEMALE)
Side B - Connector 1	(8) LC DUPLEX (MALE) WITH PULL/PUSH TAB
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N390-01M-8LC-AP](#)