

L5-30P to L5-30R Heavy-Duty Extension Cord - 30A, 125V, 10 AWG, 6 ft., Black, Locking Connectors

MODEL NUMBER: **P046-006-LL-30A**



Highlights

- Locking connectors prevent accidental disconnection
- Durable PVC jacket
- 6 ft. long
- 125V/30A rating

Package Includes

- P046-006-LL-30A Heavy-Duty Power Extension Cord, 6 ft.

Extends the length of your existing power cord with NEMA L5-30P plug by 6 ft.

Description

The P046-006-LL-30A Heavy-Duty Power Extension Cord features a NEMA L5-30P plug on one end and a NEMA L5-30R receptacle on the other, allowing you to extend the length of your existing power cord. Both molded connectors twist and lock into place, which prevents disconnection via jostling or other accidental impact. The six-foot 10 AWG cord is rated for 125V and 30A. Its durable PVC jacket is designed to last a long time.

Features

Extends Existing Power Cord with NEMA L5-30P Plug

- NEMA L5-30R receptacle at opposite end
- Molded locking connectors prevent accidental disconnection
- Integral strain relief
- 125V/30A rating
- Durable PVC jacket
- 6 ft. long

Specifications

OVERVIEW	
UPC Code	037332200938
Country/Region	North America



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Power Cord Application	PDU; UPS
INPUT	
Maximum Input Amps	30
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Voltage Compatibility (VAC)	125
Cable Length (cm)	182.88
PHYSICAL	
Power Cord Jacket Type	SJT
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Shipping Dimensions (hwd / in.)	11.500 x 9.000 x 0.500
Shipping Dimensions (hwd / cm)	29.21 x 22.86 x 1.27
Shipping Weight (lbs.)	1.9000
Shipping Weight (kg)	0.86
Color	Black
Number of Conductors	3
ENVIRONMENTAL	
Operating Temperature Range	41 F TO 95 F (5 C TO 35 C)
Storage Temperature Range	41 F TO 95 F (5 C TO 35 C)
Operating Humidity Range	0-65% RH
Storage Humidity Range	0-65% RH
CONNECTIONS	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-30R
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P046-006-LL-30A](#)