

## External 240V 3U Rack/Tower Battery Pack Enclosure + DC Cabling for select UPS Systems (BP240V10RT3U)

MODEL NUMBER: **BP240V10RT3U**



Need more runtime? The BP240V10RT3U external battery pack extends the runtime of compatible Tripp Lite UPS Systems and has a rear connector for daisy-chaining multiple battery packs together to achieve an even longer runtime. Installation is quick, simple and versatile—the battery pack can be adapted to rackmount (3U), tower or stack form factors.

### Description

BP240V10RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 240V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - SU6000RT3U, SU6000RT3UHV, SU8000RT3U, SU8000RT3U1TF, SU8000RT3UG, SU8000RT3UHW, SU8000RT3UN50, SU8000RT3UN50TF, SU10000RT3U, SU10000RT3U2TF, SU10000RT3UG, SU10KRT3U, SU10KRT3UHV, SU10K3/1INTPM, SU16KRT, SU16KRT-1TF, SU16KRT8, SU16KRTG, SU16KRTHW, SU20KRT, SU20KRT-1TF, SU20KRT8, SU20KRTG, SU20KRTHW and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Offers extended-run UPS operation when used in conjunction with compatible 240V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 240V external battery packs to

### Highlights

- Extends the runtime of expandable 240V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

### Package Includes

- BP240V10RT3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

the host UPS

- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced 2 point center-mounting in 2 post equipment racks
- 2-9USTAND option enables upright tower placement

## Specifications

| OVERVIEW  |  |
|---|--|
| UPC Code  | 037332115843   |
| INPUT   |  |
| Input Phase   | Single-Phase   |
| BATTERY   |  |
| Expandable Battery Runtime                                    | Includes a second input/output connector to daisy-chain multiple battery packs   |
| Expandable Runtime  | Yes  |
| DC System Voltage (VDC)                                       | 240  |
| UPS Connection  | Detachable cable with UPS specific DC connector (91.4 cm length, 6 gauge)  |
| Typical Battery Lifespan                                      | 4-6 years typical (North America)  |
| PHYSICAL  |  |
| External Battery Pack Form Factor                             | Rack/Tower   |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount   |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2 post rackmount</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ) |
| Material of Construction                                      | Steel  |
| Minimum Required Rack Depth (cm)                              | 83.82  |
| Minimum Required Rack Depth (inches)                          | 33   |
| Rack Height   | 3U   |
| Shipping Dimensions (hwd / cm)                                | 29.21 x 58.42 x 83.82  |
| Shipping Dimensions (hwd / in.)                               | 11.50 x 23.00 x 33.00  |
| Shipping Weight (kg)  | 83.46  |
| Shipping Weight (lbs.)  | 184.00   |
| Unit Dimensions (hwd / cm)                                    | 13.34 x 44.45 x 63.5   |
| Unit Dimensions (hwd / in.)                                   | 5.25 x 17.5 x 25   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|   |  |
|---|--|
| Unit Weight (kg)                        | 71.99  |
| Unit Weight (lbs.)                      | 158.70   |
| <b>STANDARDS &amp; COMPLIANCE</b>       |  |
| Certifications                          | Tested to CE; RoHS Compliant                                     |
| <b>WARRANTY</b>                         |  |
| Product Warranty Period (U.S. & Canada) | 2-year limited warranty  |
| Product Warranty Period (International) | 1-year limited warranty  |
| Product Warranty Period (Mexico)        | 1-year limited warranty  |
| Product Warranty Period (Puerto Rico)   | 1-year limited warranty  |
| Optional Coverage                       | 3 year, 5 year, next day and on-site warranty coverage available |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[BP240V10RT3U](#)