

Datashield Serial In-Line Surge Protector, DB25

MODEL NUMBER: **DB25-ALL**



Highlights

- Complete serial port (DB25) surge protection
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

Applications

- Ideal for the protection of data terminals, data communications equipment, PCs, printers, modems and more.

Package Includes

- DB25-ALL dataline protector
- Instruction manual and warranty information

Description

Tripp Lite's DB25-ALL offers dataline surge suppression for any DB25 serial port, regardless of cable configurations. Connects and protects all 25 pins plus D shell chassis for universal protection of any DB25 application. User configurable for use with male or female captive DB25 port. Convenient DB25 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges, faulty wiring or lightning away from network interface connections. Tripp Lite network surge suppressors reduce blown interface connections, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

SUPPRESSION: Reversible DB9 m/f jacks, protects pins 1-25 and chassis, 18V clamping

Features

- DB25 protects 25 pin serial connections for dataline surge suppression of data terminal, data communications equipment and PCs, printers, modems and more
- Reversible for use with male or female captive DB25 ports
- Offers protection on all 25 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

Specifications

OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	340
USB Charging	No
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Connection Type	DB25
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	18
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-25 & Chassis
PHYSICAL	
Metal Case	No
SPECIAL FEATURES	
Right-Angle Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DB25-ALL](#)