

7-Outlet Home/Business Theater Surge Protector, 6-ft. Cord, 2100 Joules, Tel/Modem/Coax Protection

MODEL NUMBER: HT706TSAT



Description

Tripp Lite's HT706TSAT Home/Business Theater Surge Suppressor provides high-performance protection—2100 joules—stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 7 outlets (with transformer spacing), 2-line 2.2 GHz coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$100,000 Ultimate Lifetime Insurance coverage (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. cord with a right-angle plug, 6 ft. coaxial cable and 6 ft. phone cord.

Features

- 2100 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected components against surge damage...for life!
- 7 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 4 transformers
- 2 sets of surge-protected 2.2 GHz gold coaxial connectors (with included 6 ft. gold coaxial cable)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 6 ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Integrated circuit breaker protects against dangerous system overload
- High-impact plastic housing (black) stands up to the most demanding environments
- UL and CSA listed

Specifications

Highlights

- 7 outlets / 6 ft. cord
- 2100 joule rating
- 2-line 2.2 GHz gold coaxial surge protection
- 1-line tel/modem surge protection
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Perfect for small home/business theater installations:
high-definition TVs, satellite and A/V receivers, DVD/CD players and more

Package Includes

- HT706TSAT Home/Business Theater Surge Suppressor
- 6 ft. gold coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(7) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Accommodates 4 transformers
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	75000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm protection and grounding status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2100
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400, 400, 500
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable (Coax) Protection Details	2 line
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2 x 15 x 6
Shipping Dimensions (hwd / cm)	5.08 x 38.1 x 15.24
Shipping Weight (lbs.)	1.8
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	1.5 x 14 x 3.25
Unit Dimensions (hwd / cm)	3.81 x 35.56 x 8.26
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots allow desk or wall mounting
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	Distance between transformer outlet and standard outlet = 38.10mm; Distance between standard outlets = 25.40mm
Keyhole Slot Mounting Measurement (Center to Center)	160mm
Metal Case	No
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	CSA
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance
---	---

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[HT706TSAT](#)