

Isobar Surge Suppressor - Premium surge, spike and line noise protection

MODEL NUMBER: **IB4-6/220**



Specifications

OVERVIEW	
Intended Application	Home/Office; Computer Networks
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	9
Outlet Quantity / Type	4 NEMA 5-15R
Number of Outlets	4
Transformer Accommodation	Supports up to 2 large transformer plug accessories without covering remaining outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	230V (220-250V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Voltage Compatibility (VAC)	230



Maximum Surge Amps	22000
LEDS ALARMS & SWITCHES	
Switches	Two position red illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	330
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	300
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
Isolated Filter Banks	Unique isolated filter bank design offers additional filtering between each duplex pair of outlets on the strip to prevent electrical noise interference between connected loads. Includes 2 filter banks.
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	3.5 x 7 x 2.5
Unit Dimensions (hwd / cm)	8.9 x 17.8 x 6.4
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Metal end caps are fitted with keyhole mounting tabs for wallmount installation
Housing Color	Light Gray
Receptacle Color	Black
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 39.30mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 131.90mm; Distance between vertical tabs = 58.17mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[IB4-6/220](#)