

USB to 5V DC Type-M Barrel Plug Power Cord - M/M, 28 AWG, Black, 3 ft. (0.91 m)

MODEL NUMBER: **U152-003-M**



USB to 5V DC power cable plugs into your 5V DC mobile device, so you can power and charge it through a computer or laptop's USB port.

Features

USB to DC Power Cable with USB-A to Type M Barrel Plug Connection You don't need to carry around a wall adapter to keep your 5V DC mobile device charged. This USB to 5V DC power cable features a male USB-A plug for connecting to a computer USB port and a male 5.5 mm (OD) x 2.1 mm (ID) Type M barrel plug for connecting to a mobile device. The U152-003-M is ideal for powering and/or charging a compatible security camera, switch, router, external hard drive, media player or other mobile device. Its three-foot length makes it convenient to carry in your backpack or laptop bag, instead of dragging around each mobile device's wall charger. Polarity: positive tip, negative sleeve.

Highlights

- USB to DC power cable is ideal for charging DC power devices from your laptop
- Great accessory for smartphones, hard drives, media players and other compatible devices
- USB-A plug connects to computer or laptop; Type M barrel plug connects to device
- More convenient charging solution than storing or carrying multiple device chargers
- 3-ft. (0.91 m) cable fits easily into backpack or laptop bag for charging on the go

Applications

- Power a security camera or other Type M network device from the USB port on a convenient laptop
- Connect an external hard drive to your laptop, eliminating the need to find a nearby outlet for the drive's bulky wall charger
- Charge a compatible smartphone or other mobile peripheral using your computer
- Plug your MP3 player or other media player into your vehicle's USB port to listen to a customized playlist

Package Includes

- U152-003-M USB to 5V DC Power Cable, 3 ft., Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332182616
Technology	USB
Country/Region	Global
INPUT	
Maximum Input Amps	0
PHYSICAL	
Color	Black
Number of Conductors	0
Wire Gauge (OD - mm ²)	0
Cable Length (ft.)	3
Cable Length (m)	0.9
Power Cord Jacket Type	Null
Shipping Dimensions (hwd / cm)	0.13 x 13.21 x 22.61
Shipping Dimensions (hwd / in.)	0.05 x 5.20 x 8.90
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.05
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	TYPE M 5V DC
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U152-003-M](#)