

Hi-Speed USB to IEEE 1284 Parallel Printer Gold Adapter Cable (USB-A to DB25 M/F), 6 ft. (1.83 m)

MODEL NUMBER: U207-006



Features

- Converts USB to IEEE-1284 Parallel DB25 Female
- Bus Powered - No external power required
- Plug-n-Play Installation for Windows 2000 / XP / Vista / WIN7 / WIN8 / WIN10
- USB 1.1 Compliant
- Bus Powered - No External Power Supply needed

Specifications

OVERVIEW	
UPC Code	037332155764
Technology	DB25; USB; Parallel
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	17.02 x 11.94 x 0.25
Shipping Dimensions (hwd / in.)	6.70 x 4.70 x 0.10
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30

Highlights

- Converts USB to IEEE-1284 Parallel DB25 Female
- Bus Powered - No external power required
- Plug-n-Play Installation

System Requirements

- USB 1.1 or 2.0 port
- Windows 2000 / XP/ Vista / WIN7 / WIN8 / WIN10 OS

Package Includes

- U207-006 USB to Parallel Printer Adapter Cable - 6-ft. (1.83 m)
- User Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB25 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U207-006](#)