

## 4-Port USB 2.0 Ultra-Mini Compact Hub with Power Adapter

MODEL NUMBER: **U222-004-R**



### Features

- USB2.0 Hub - 4-Port
- Supports all data transfer rates up to 480Mbps
- Compact design with built-in cable (6-in.), perfect for travel
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Diagnostic LEDs indicate power and port status
- Bus-powered or self-powered
- All four ports support USB Battery Charging ( BC ) specification v1.2, providing up to 1.5A for fast charging of mobile devices
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6ft USB-A to Micro-B USB 2.0 cable to connect the U222-004-R to the External Power Supply.
- Compatible with all major operating systems

### Highlights

- Link multiple USB devices to 1 computer with ultra-compact hub
- Meets or Exceeds USB 2.0 Specifications
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6-ft. (0.79 m) USB-A to Micro-B USB 2.0 Cable
- All four ports support USB Battery Charging ( BC ) specification v1.2, providing up to 1.5A for fast charging of mobile devices

### Package Includes

- U222-004-R USB2.0 4-Port Ultra-Mini Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- USB-A to Micro-B USB 2.0 Cable, 2.6-ft. (0.79 m)

## Specifications

OVERVIEW	
UPC Code	037332118127
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Technology	USB 2.0 (High Speed); USB
Host Connector	USB A (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
<b>POWER</b>	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
External Power Supply Output Specs (V / A)	5V / 2A
<b>CHARGING</b>	
Charging Ports Details	Any of the 4 ports
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(4) 1.5A
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Material of Construction	Plastic
Shipping Dimensions (hwd / cm)	2.54 x 10.16 x 12.95
Shipping Dimensions (hwd / in.)	1.00 x 4.00 x 5.10
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB A (MALE)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side B - Connector 1	(4) USB A (FEMALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS, REACH, WEEE, FCC, NOM
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U222-004-R](#)