

7-Port USB 2.0 Hub

MODEL NUMBER: **U222-007-R**



Description

Tripp Lite's ultra small 7-port USB 2.0 hub is the most versatile and powerful hub on the market. It allows you to connect up to seven USB devices to a single USB port on your computer. This unit meets or exceeds USB 2.0 Specifications for Hi-Speed data transmission rates up to 480Mbps. Perfect for both the mobile and desktop user. While the hub will function perfectly in virtually all cases without needing external power, a compact, multi-voltage AC adapter (100-240V) has been provided for the rare circumstance when connecting a power hungry device. This USB 2.0 device is backwards compatible so that it will function with both USB 2.0 and USB 1.1 devices. Over-current protection safeguards connected equipment from overvoltages. Includes stand for upright positioning.

Features

- USB2.0 7-Port Hub
- Supports data transfer rates up to 480Mbps
- Connect up to 7 USB devices to a single USB port on your computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Per-port overcurrent protection
- Bus-powered or self-powered
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- The included external power supply provides 2.5A of power, to be shared between the hub ports (up to 500mA per port)
- Compact, multi-voltage power supply (100-240V) provided
- Compatible with all major operating systems

Highlights

- Connect up to 7 USB 2.0 devices
- Hi-Speed 480Mbps data transfer
- Backward compatible with USB 1.1 devices
- Over-current protection safeguards connected equipment from overvoltages
- Supports USB 2.0 spec up to 500mA per port
- Includes base stand for upright positioning
- Compatible with all major operating systems

System Requirements

- USB 2.0 port
- Compatible with all major operating systems

Package Includes

- U222-007-R USB 2.0 7-Port Mini Hub
- Compact External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2.5A)
- 4 ft. extension cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332126733
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2.5A
Over Current Protection	Yes
Technology	USB 2.0 (High Speed); USB
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(7) USB-A - USB 2.0
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V / 2.5A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 3.5 x 1.35 x 9.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red - Power



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black; White
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	8.90 x 5.60 x 2.50
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	0.94 x 3.4 x 2.7
Unit Packaging Type	Clamshell
Unit Weight (kg)	0.09
Unit Weight (lbs.)	0.2
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	14 to 176 °F (-10 to 80 °C)
Relative Humidity	0% to 90 RH, Non-Condensing
BTUs	8.5 BTU/Hr
CONNECTIONS	
Ports	7
Side A - Connector 1	USB B (FEMALE)
Side B - Connector 1	(7) USB A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
STANDARDS & COMPLIANCE	
Approvals	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U222-007-R](#)