

USB 3.0 to SATA Hard Drive Lay-Flat Enclosure for 3.5-in. HDD and SSD

MODEL NUMBER: **U339-001-FLAT**



Quickly and easily add storage and transfer data to your computer or laptop by connecting a SATA drive to your computer's USB port. Compact lay-flat design takes up little space and maintains stability on most surfaces.

Description

The U339-001-FLAT USB 3.0 to SATA Hard Drive Lay-Flat Enclosure allows you to quickly and easily add storage and transfer data to your computer or laptop from a SATA hard drive. It lays flat to take up little space and maintain stability. Just insert a 2.5-in. or 3.5-in. SATA HDD (Hard Disk Drive) or SSD (Solid State Drive) into the slot, and connect the included 4-ft. (1.22 m) USB 3.0 cable to the USB port on your computer. Slide the protective cover over the dock, even when it's in use, to keep the SATA drive dust-free at all times. The docking station accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives. It supports USB 3.0 (5 Gbps), USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds, as well as UASP (USB Attached SCSI Protocol), which transfers data faster than conventional USB 3.0 and requires a UASP-enabled host controller. Plug-and-play configuration means it works right out of the box with no software or drivers to download or install. Green LED indicates the unit is connected to a USB port. Blue LED indicates the unit is receiving power. Works with Windows and Mac.

Features

Easy to Use Right from the Box

- Lays flat for stable performance
- Plug and play—no extra software or drivers to download or install
- SATA drive slides easily into convenient slot
- Protective cover keeps dust and dirt away from sensitive SATA drives
- On/off button powers off SATA drive when not in use
- LEDs indicate when the unit is powered on and connected

Highlights

- Compact, stable lay-flat design
- No software or drivers to download or install
- Compliant with USB 3.0, USB 2.0 and USB 1.1 transfer rates
- Compliant with SATA HDD or SSD drives up to SATA III
- Protective cover keeps SATA drive free of dust

System Requirements

- Computer with available USB port (USB 3.0 port required to achieve USB 3.0 data transfer speeds)
- 2.5-in. or 3.5-in. SATA HDD or SSD
- UASP-enabled host controller (for UASP data transfer speeds only)

Package Includes

- U339-001-FLAT USB 3.0 to SATA Hard Drive Lay-Flat Enclosure
- USB 3.0 A/B cable, 4-ft. (1.22 m) length
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60 Hz, 0.8A; Output: 12V, 2A, 5-ft. (1.52 m))
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Compliant with Most Applications

- Accepts 2.5-in. or 3.5-in. SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives
- Supports USB 3.0 (5 Gbps), USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds
- Supports UASP (USB Attached SCSI Protocol) for even faster transfer speeds than USB 3.0*
- Works with both HDD (Hard Disk Drive) and SSD (Solid State Drive)

**Requires UASP-enabled host controller. UASP is supported by Windows 8 and later, Mac OS X 10.8 and later, and Linux.*

Specifications

OVERVIEW	
UPC Code	037332188120
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A, 5 ft.
Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.33 x 21.08 x 20.57
Shipping Dimensions (hwd / in.)	2.10 x 8.30 x 8.10
Shipping Weight (kg)	0.54
Shipping Weight (lbs.)	1.20
ENVIRONMENTAL	
Operating Temperature Range	41 to 104 F (5 to 40 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	8 to 90%
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U339-001-FLAT](#)